Product datasheet

Specifications

Sreen Premium™



modular analog voltmeter iVLT - 0..500 V

16061

Main

Range	Acti9
Device Short Name	iVLT
Product Or Component Type	Voltmeter
Range Compatibility	Prisma Prisma P door Prisma Prisma G door
Scale	0-500 V
Technology Type	Ferromagnetic
Scale Type	Pseudo-linear scale over 90°
Mounting Support	DIN rail

Complementary

Type Of Measurement	Voltage
Accuracy Class	Class 1.5
Power Consumption In Va	3.5 VA
Power Consumption In Va	3.5 VA
Overload Withstand	1.2 Un, permanently 2 Un, 5 s
9 Mm Pitches	8
Width	70 mm
Height	83 mm
Depth	66 mm
Temperature Drift	+/- 0.03 %/°C
Connections - Terminals	Tunnel type terminalrigid 1.56 mm ²

Environment

Standards	IEC 61010-1 IEC 61000-4 IEC 60051-1
Ambient Air Temperature For Operation	-2550 °C
Reference Temperature	23 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	7.8 cm
Package 1 Width	7.5 cm
Package 1 Length	9.3 cm
Package 1 Weight	163.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	45
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.781 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information