

Product datasheet

Specifications



Carriage switch, MasterPact NT/
NW, ComPacT NS, drawout,
chassis test position (CT), 1 NO/NC,
standard, 8A/240VAC

33752

Main

Device Short Name	test position contact
Product Or Component Type	Auxiliary contact
Device Application	Monitoring
Range Compatibility	Masterpact MasterPact NT Masterpact MasterPact NW Masterpact MasterPact NW DC ComPact ComPact NS630b...1600
Signal Contacts Composition	1 NO/NC

Complementary

Auxiliary Contacts Type	Standard
Auxiliary Contacts Operation	Test position
Mounting Mode	Drawout
[Ie] Rated Operational Current	AC-12: 6 A at 690 V AC 50/60 Hz AC-12: 8 A at 240 V AC 50/60 Hz AC-12: 8 A at 380 V AC 50/60 Hz AC-12: 8 A at 480 V AC 50/60 Hz DC-12: 0.8 A at 125 V DC DC-12: 2.5 A at 24/48 V DC DC-12: 0.3 A at 150 V DC
Minimum Load	100 mA at 24 V

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.9 cm
Package 1 Width	4.2 cm
Package 1 Length	4.2 cm
Package 1 Weight	1.018 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information