
Product datasheet

Specifications





Communicating motor mechanism module (MCH), drawout ComPacT NS630b to NS1600, 48/60VDC, 48VAC 50/60Hz

33838

Main

mam	
Device Short Name	MCH
Product Or Component Type	Motor mechanism
Device Application	Automatic spring charging
Range Compatibility	ComPacT new generation ComPact NS630b1600
Control Type	Communicating
[Uc] Control Circuit Voltage	48 V AC 50/60 Hz 4860 V DC
Circuit Breaker Mounting Mode	Drawout
Circuit Breaker Frame Rated Current	1600 A 630 A 1250 A 800 A 1000 A

Complementary

Control Signal Type	Impulse Maintained
Circuit Breaker Response Time	60 ms +/- 10 ms open 60 ms +/- 10 ms closed
Maximum Operating Frequency	<= 3 cycles per minute
Maximum Power Consumption In Va	180 VA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	13.0 cm
Package 1 Length	18.0 cm
Package 1 Weight	1.414 kg

Contractual warranty

Warranty	18 months
----------	-----------



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Rohs Exemption Information

Yes



Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information