Product datasheet





Circuit breaker frame, MasterPact NW20L1, 2000A, 150kA/440VAC 50/60Hz (Icu), 4 poles, drawout, without control unit

48297

Main

Range	MasterPacT
Product Name	MasterPact NW
Circuit Breaker Name	MasterPact NW20L1
Product Or Component Type	Circuit breaker
Device Application	Power distribution protection
Poles Description	4P
Neutral Position	Left
Control Unit	Without control unit
[In] Rated Current	2000 A at 40 °C
Performance Type	L1 150 kA 440 V AC
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Selectivity Category	Category B
Control Type	Push-button
Mounting Mode	Drawout

Complementary

[Icu] Rated Ultimate Short-Circuit Breaking Capacity	150 kA at 220/415 V AC 50/60 Hz 130 kA at 440 V AC 50/60 Hz 100 kA at 525 V AC 50/60 Hz
[Ics] Rated Service Breaking Capacity	150 kA at 220/415 V AC 50/60 Hz 130 kA at 440 V AC 50/60 Hz 100 kA at 525 V AC 50/60 Hz
[Icw] Rated Short-Time Withstand Current	30 kA 1 s 30 kA 3 s
[Icm] Rated Short-Circuit Making Capacity	330 kA 220/415 V AC at 50/60 Hz 330 kA 440 V AC at 50/60 Hz 286 kA 525 V AC at 50/60 Hz 220 kA 690 V AC at 50/60 Hz
Integrated Instantaneous Protection (Din In Ka Peak)	7288 kA
Sensor Rating	1000 A 2000 A
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	12 kV
Power Dissipation In W	470 W

Life Is On Schneider 25 Apr 2024

Maximum Breaking Time	10 ms
Maximum Closing Response Time	70 ms
Mounting Support	Backplate
	Rails
Upside Connection	Front
	Rear
Downside Connection	Front
	Rear
Connection Pitch	115 mm
Mechanical Durability	10000 cycles without maintenance
	20000 cycles with maintenance
Electrical Durability	3000 cycles 690 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-2 3000 cycles 440 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-2
Height	439 mm
Width	556 mm
Depth	395 mm
Net Weight	120 kg
Standards	EN/IEC 60947-1
	EN/IEC 60947-2
Product Certifications	CE
	CCC
	EAC

Environment

Ip Degree Of Protection	IP30 conforming to IEC 60529
Pollution Degree	4 conforming to IEC 60664-1
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C
Operating Altitude	02000 m without derating 2000 m5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	33.0 cm
Package 1 Width	52.0 cm
Package 1 Length	30.0 cm
Package 1 Weight	51.182 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information