Product datasheet

Specification





Control unit MicroLogic 6.0A, MasterPact NW drawout, selective and earth fault protections (LSIG), ammeter

48361

Main

| wain | |
|--------------------------------|---|
| Range | MasterPact |
| Range Of Product | MasterPact NW |
| Product Or Component Type | Control unit |
| Trip Unit Name | MicroLogic 6.0 A |
| Trip Unit Technology | Electronic |
| Range Compatibility | Masterpact NW0840 Masterpact NW40b63 Masterpact NW H10 Masterpact NW H2 corrosion protection |
| Device Application | Distribution |
| Number Of Poles | 4P 3P |
| Protected Poles Description | 4t 3t 3t + N/2 |
| Trip Unit Protection Functions | Selective + earth-fault protection |
| Protection Type | for overload protection (long time) for short time short-circuit protection for instantaneous short-circuit protection for earth fault |
| Trip Unit Rating | 800 A at 50 °C 1000 A at 50 °C 1250 A at 50 °C 1600 A at 50 °C 2000 A at 50 °C 2500 A at 50 °C 3200 A at 50 °C 4000 A at 50 °C 5000 A at 50 °C 6300 A at 50 °C |
| Network Type | AC |
| Network Frequency | 50/60 Hz |
| Circuit Breaker Mounting Mode | Drawout |

Complementary

| <u> </u> | |
|--|---|
| Long-Time Pick-Up Adjustment Type Ir (Thermal Protection) | Adjustable 9 settings |
| [Ir] Long-Time Protection Pick-Up Adjustment Range | 0.41 x ln |
| Long-Time Protection Delay Adjustment Type Tr | Adjustable 9 settings |
| [Tr] Long-Time Protection Delay Adjustment Range | 0.716.6 s at 7.2 x lr 0.724 s at 6 x lr 12.5600 s at 1.5 x lr |

25 Apr 2024 Life Is On Schneider

| Thermal Memory | 20 mn |
|---|--|
| Short-Time Protection Pick-Up Adjustment Type Isd | Adjustable 9 settings |
| [Isd] Short-Time Protection Pick- Up Adjustment Range | 1.510 x lr |
| Short-Time Protection Delay Adjustment Type Tsd | Adjustable |
| [Tsd] Short-Time Protection Delay Adjustment Range | 00.4 s l²t=off 0.10.4 s l²t=on |
| Instantaneous Protection Pick-Up Adjustment Type Ii | Adjustable 9 settings |
| [li] Instantaneous Protection Pick- Up Adjustment Range | 215 x ln Off |
| Ground-Fault Protection Pick-Up Adjustment Type Ig | Adjustable 9 settings |
| [Ig] Ground-Fault Protection Pick- Up Adjustment Range | 0.21 x In for 400 A < In < 1250 A 0.31 x In for In <= 400 A 5001200 A for In >= 1250 A |
| Ground-Fault Protection Time Delay Adjustment Type Tg | Adjustable |
| [Tg] Ground-Fault Protection Time Delay Adjustment Range | 00.4 s l²t=off 0.10.4 s l²t=on |
| Earth-Leakage Protection | Without |
| Zone Selective Interlocking Zsi | With |
| Local Signalling | 3 LEDs (red) for electrical fault 1 LED (red) for internal error |
| Display Type | Digital display |
| Type Of Measurement | Ammeter |
| Communication Of Data | Measurement readout Protection and alarm settings |

Environment

| Ambient Air Temperature For Operation | -2570 °C |
|---------------------------------------|----------|
| Ambient Air Temperature For Storage | -4085 °C |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 6.8 cm |
| Package 1 Width | 8.0 cm |
| Package 1 Length | 21.5 cm |
| Package 1 Weight | 369.0 g |

Contractual warranty

| Warranty | 18 months |
|----------|-----------|



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| | Mercury Free | |
|----------|----------------------------|-----|
| ⊘ | Rohs Exemption Information | Yes |
| ⊘ | Pvc Free | |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |