# **Product datasheet**





## Control unit MicroLogic 7.0A, MasterPact NW drawout, selective and earth leakage protections (LSIV), ammeter

48362

#### Main

wain	
Range	MasterPact
Range Of Product	MasterPact NW
Product Or Component Type	Control unit
Trip Unit Name	MicroLogic 7.0 A
Trip Unit Technology	Electronic
Range Compatibility	Masterpact NW0840 Masterpact NW40b63 Masterpact NW H10 Masterpact NW H2 corrosion protection
Device Application	Distribution
Number Of Poles	4P 3P
Protected Poles Description	4t 3t 3t + N/2
Trip Unit Protection Functions	Selective + earth-leakage protection
Protection Type	for overload protection (long time) for short time short-circuit protection for instantaneous short-circuit protection for earth-leakage protection
Trip Unit Rating	800 A at 50 °C 1000 A at 50 °C 1250 A at 50 °C 1600 A at 50 °C 2000 A at 50 °C 2500 A at 50 °C 3200 A at 50 °C 4000 A at 50 °C 5000 A at 50 °C 6300 A at 50 °C
Network Type	AC
Network Frequency	50/60 Hz
Circuit Breaker Mounting Mode	Drawout

### Complementary

Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings	
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.41 x ln	
Long-Time Protection Delay Adjustment Type Tr	Adjustable 9 settings	
[Tr] Long-Time Protection Delay Adjustment Range	0.716.6 s at 7.2 x lr 0.724 s at 6 x lr 12.5600 s at 1.5 x lr	

Life Is On Schneider 25 Apr 2024



Thermal Memory	20 mn	
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable 9 settings	
[Isd] Short-Time Protection Pick- Up Adjustment Range	1.510 x lr	
Short-Time Protection Delay Adjustment Type Tsd	Adjustable	
[Tsd] Short-Time Protection Delay Adjustment Range	00.4 s l²t=off 0.10.4 s l²t=on	
Instantaneous Protection Pick-Up Adjustment Type Ii	Adjustable 9 settings	
[li] Instantaneous Protection Pick- Up Adjustment Range	Off 215 x ln	
Earth-Leakage Protection	Integrated	
Earth-Leakage Protection Sensitity Adjustment Type Ιδη	Adjustable 9 settings	
[lδn] Earth-Leakage Protection Sensitivity Adjustment Range	0.530 A	
Earth-Leakage Sensitivity	10 A for class A 30 A for class AC	
Earth-Leakage Protection Time Delay Adjustement Type Δt	Adjustable 5 settings	
[Δt] Earth-Leakage Protection Time Delay Adjustment Range	60800 ms	
Zone Selective Interlocking Zsi	With	
Local Signalling	3 LEDs (red) for electrical fault 1 LED (red) for internal error	
Display Type	Digital display	
Type Of Measurement	Ammeter	
Communication Of Data	Measurement readout Protection and alarm settings	

### **Environment**

Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	22.0 cm
Package 1 Length	7.0 cm
Package 1 Weight	429.0 g

## **Contractual warranty**

Warranty	10 months
wairanty	18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information