


Product datasheet

Specifications



Standard opening voltage release
MX, MasterPact NW drawout,
24/30VDC, 24VAC

48491

Main

Range	MasterPacT
Range Of Product	MasterPact NW MasterPact NW DC
Device Short Name	MX
Product Or Component Type	Voltage release
Device Application	Control
Voltage Release Type	Opening coil Instantaneous voltage release
Control Type	Standard
[Uc] Control Circuit Voltage	24 V AC 50/60 Hz 24...30 V DC
Circuit Breaker Mounting Mode	Drawout
Range Compatibility	Masterpact MasterPact NW Masterpact MasterPact NW DC

Complementary

Operating Threshold	0.7...1.1 x Un opening
Response Time	50 ms +/- 10 %
Supply Holding Power	4.5 VA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	6.1 cm
Package 1 Length	8.3 cm
Package 1 Weight	1.166 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information