





Push-button head, Harmony 9001SK, plastic, without mushroom, 30mm, 3 positions, return to center

9001SKR8

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Head for push-button
Device Short Name	9001SK

Complementary

Bezel Material	Plastic	
Mounting Diameter	30 mm	
Shape Of Signaling Unit Head	Octagonal	
Light Source	without	
Light Block Supply	Without supply	
Contacts Type And Composition	Without contact block	
Product Certifications	UL listed file E42259 CCN NKCR CE CSA LR24590 class 3211 03	
Ip Degree Of Protection	IP64	
Nema Degree Of Protection	NEMA 1/2/3/3R/4/4X/6/12/13	
Cap/Operator Or Lens Colour	ns Colour Without mushroom	
Type Of Operator	perator Pull : spring return, center : stay put, push : spring return	
Operator Position Information	3 positions	
Size	30 mm	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.826 cm
Package 1 Width	5.842 cm
Package 1 Length	11.43 cm
Package 1 Weight	63.503 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations