Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product datasheet

Specifications





iCT 63A 4NO 24V 50Hz contactor

A9C20164

Main

Range Of Product	Acti9
Product Name	Acti9 iCT
Product Or Component Type	Contactor
Device Short Name	iCT
Device Application	Motor-heating-lighting
Poles	4P
[le] Rated Operational Current	63 A AC-7A 20 A AC-7B
Pole Contact Composition	4 NO
Network Type	AC
Control Type	Remote control
[Uc] Control Circuit Voltage	24 V AC 50 Hz

Complementary

Network Frequency	50 Hz
[Ue] Rated Operational Voltage	400 V AC 50 Hz
Maximum Power	2.1 W at 400 V AC
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	4 kV
Control Signal Type	Maintained
Switching Frequency	100 switching operations/day
Local Signalling	Action indicator
Hold-In Power Consumption In Va	6.5 VA
Inrush Power In Va	53 VA
Mounting Mode	Clip-on
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	6
Height	85 mm
Width	54 mm
Depth	68.5 mm
Colour	White

Mechanical Durability	1000000 cycles	
Electrical Durability	100000 cycles IEC/EN 61095 63 A 50 Hz AC-7A	
	30000 cycles IEC/EN 61095 20 A 50 Hz AC-7B	
	30000 cycles IEC/EN 61095 50 Hz AC-7C	
	100000 cycles EN/IEC 60947-4-1 50 Hz AC-1	
	30000 cycles EN/IEC 60947-4-1 50 Hz AC-3	
	30000 cycles EN/IEC 60947-4-1 50 Hz AC-5a	
	30000 cycles EN/IEC 60947-4-1 50 Hz AC-5b	
Connections - Terminals	Control circuit: tunnel type terminals2 cable(s) 1.5 mm² rigid	
	Control circuit: tunnel type terminals1 cable(s) 1.52.5 mm² rigid	
	Power circuit: tunnel type terminals1 cable(s) 616 mm² flexible	
	Power circuit: tunnel type terminals1 cable(s) 625 mm² rigid	
	Control circuit: tunnel type terminals2 cable(s) 1.52.5 mm² flexible	
Tightening Torque	Control circuit: 0.8 N.m	
	Power circuit: 3.5 N.m	
Product Compatibility	IACTc	
	IATEt	
	IACTp	
	IACTs	
Compatibility Code	ICT	
Market Segment	Small commercial	
	Residential	

Environment

Standards	IEC/EN 61095
Noise Level	30 dB
Heat Dissipation	2.1 W at 50/60 Hz
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	2
Tropicalisation	2 conforming to EN 60947-4-1 2 conforming to EN 61095 2 conforming to IEC 1095
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-560 °C
Ambient Air Temperature For Storage	-4070 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11 cm
Package 1 Width	6 cm
Package 1 Length	12 cm
Package 1 Weight	357 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	4
Package 2 Height	11.5 cm
Package 2 Width	12.5 cm
Package 2 Length	25 cm

Package 2 Weight	1.504 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	24
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	9.496 kg

Contractual warranty

Warranty 18 months

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations