Product datasheet

Specification





Acti9, Residual current circuit breaker (RCCB), Acti9 iID, 2P, 63A, A-SI type, 300mA, selective

A9R35263

Main

| Range | Acti9 |
|-------------------------------------|-----------------------------------------|
| Product Name | Acti9 iID |
| Product Or Component Type | Residual current circuit breaker (RCCB) |
| Device Short Name | ilD |
| Poles Description | 2P |
| Neutral Position | Left |
| [In] Rated Current | 63 A |
| Network Type | AC |
| Earth-Leakage Sensitivity | 300 mA |
| Earth-Leakage Protection Time Delay | Selective |
| Earth-Leakage Protection Class | Type A-SI (Super Immunised) |

Complementary

| Device Location In System | Outgoer |
|-----------------------------------------|-------------------------|
| Network Frequency | 50/60 Hz |
| [Ue] Rated Operational Voltage | 220240 V AC 50/60 Hz |
| Residual Current Tripping Technology | Voltage independent |
| Rated Breaking And Making Capacity | Idm 1500 A Im 1500 A |
| Rated Conditional Short-Circuit Current | 10 kA |
| [Ui] Rated Insulation Voltage | 500 V AC 50/60 Hz |
| [Uimp] Rated Impulse Withstand Voltage | 6 kV |
| Contact Position Indicator | Yes |
| Control Type | Toggle |
| Mounting Mode | Clip-on |
| Mounting Support | DIN rail |
| 9 Mm Pitches | 4 |
| Height | 91 mm |
| Width | 36 mm |
| Depth | 73.5 mm |
| Net Weight | 0.21 kg |
| | |

| Colour | White | |
|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| Mechanical Durability | 20000 cycles | |
| Electrical Durability | AC-1: 15000 cycles | |
| Locking Options Description | Padlocking device | |
| Connections - Terminals | Single terminal top or bottom 135 mm² rigid Single terminal top or bottom 125 mm² flexible Single terminal top or bottom 125 mm² flexible with ferrule | |
| Wire Stripping Length | 14 mm for top or bottom connection | |
| Tightening Torque | 3.5 N.m top or bottom | |

Environment

| Standards | EN/IEC 61008-1 | |
|---------------------------------------|-------------------------------------------------------------------------------|--|
| Product Certifications | EAC | |
| Ip Degree Of Protection | IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529 | |
| Pollution Degree | 3 | |
| Electromagnetic Compatibility | 8/20 μs impulse withstand, 3000 A conforming to EN/IEC 61008-1 | |
| Ambient Air Temperature For Operation | -2560 °C | |
| Ambient Air Temperature For Storage | -4085 °C | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.000 cm |
| Package 1 Width | 8.200 cm |
| Package 1 Length | 9.700 cm |
| Package 1 Weight | 214.000 g |
| Unit Type Of Package 2 | \$03 |
| Number Of Units In Package 2 | 54 |
| Package 2 Height | 30.000 cm |
| Package 2 Width | 30.000 cm |
| Package 2 Length | 40.000 cm |
| Package 2 Weight | 12.482 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |