Product datasheet

Specifications





network module, Modicon M580, Ethernet IP/Modbus TCP

BMENOC0301

Main

Range Of Product	Modicon M580
Product Or Component Type	Communication module
Product Compatibility	BMEXBP Ethernet + X-bus rack
Concept	Transparent Ready

Complementary

Integrated Connection Type	3 Ethernet, connector type: RJ45, transmission rate: 10/100 Mbit/s, transmission mode: double shielded twisted pair
Web Server	Basic
Transmission Support Medium	Ethernet backplane
Communication Service	Bandwidth management
	FDR server
	SNMP network administrator
	Modbus TCP I/O Scanner and Messaging
	Ethernet/IP I/O Scanner and Messaging
	RSTP support
	Port mirroring
	Embedded multiport switch
Port Ethernet	10BASE-T/100BASE-TX
Supply	Internal power supply via rack
Marking	CE
Module Format	Standard
Current Consumption	900 mA at 3.3 V DC (for product version >= 13)
	1800 mA at 3.3 V DC (for product version < 13)
Net Weight	0.2 kg

Environment

Ambient Air Temperature For Operation	060 °C
Ip Degree Of Protection	IP20
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Local Signalling	 LED (green) for processor running (RUN) LED (red) for processor or system fault (ERR) LED (green/red) for ETH MS (Ethernet port configuration status) LED (green/red) for Eth NS (Ethernet network status)

Packing Units

Unit Type Of Package 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	11.200 cm
Package 1 Length	12.000 cm
Package 1 Weight	254.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	15
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.136 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards


Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	

Product datasheet

Dimensions Drawings

Modules Mounted on Racks

Dimensions



(1) With removable terminal block (cage, screw or spring).

(2) With FCN connector.

(3) On AM1 ED rail: 35 mm wide, 15 mm deep. Only possible with BMXXBP0400/0400H/0600/0600H/0800/0800H rack.

Iduk.		
Rack references	a in mm	a in in.
BMXXBP0400 and BMXXBP0400H	242.4	09.54
BMXXBP0600 and BMXXBP0600H	307.6	12.11
BMXXBP0800 and BMXXBP0800H	372.8	14.68
BMXXBP1200 and BMXXBP1200H	503.2	19.81