

Product datasheet

Specifications



EVlink Wallbox - 22 kW - T2 socket outlet with shutter - charging station

EVH2S22P04K

Main

Range	EVlink
Product name	EVlink Wallbox
Product or component type	Charging station
Device short name	EVH2
Poles description	3P + N
Mounting mode	Wall-mounted
Offer type	Standard
Max power	22 kW 32 A
Number of charge point	1
Connection to the vehicle	Socket-outlet T2 with shutter
Access control system	Key

Complementary

Rated supply voltage	380...415 V AC 50/60 Hz
Earthing system	TT TN
Number of inputs	1
Input type	Contact for power limitation Contact for delayed charging
Control type	1 white button, function: stop/restart Green button, function: cable unlocking
Local signalling	1 multi-colour LED, function: status indication
Height	480 mm
Width	331.5 mm
Depth	170 mm
Net weight	5.6 kg
Colour	White (RAL 9003) Grey (RAL 7016)
Standards	IEC 62196-2 IEC 62196-1 IEC 61851-1 IEC 61851-22
Product certifications	CB CE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

IP degree of protection	IP54 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for operation	-30...50 °C
Ambient air temperature for storage	-40...80 °C
Relative humidity	5...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	8.12 kg
Package 1 Height	26 cm
Package 1 width	40 cm
Package 1 Length	53.5 cm
Unit Type of Package 2	P06
Number of Units in Package 2	4
Package 2 Weight	41.94 kg
Package 2 Height	50 cm
Package 2 width	80 cm
Package 2 Length	60 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information