

# Product datasheet

Specifications



## Attached Cable T2 32A 3-Ph IEC 4 meters - Wallbox EVH2 spare part

EVP2CNS323C4

### Main

Range	EVlink
Product Or Component Type	Charging cable
Accessory / Separate Part Category	Spare part
Network Number Of Phases	Three phase
Poles Description	3P + N
[In] Rated Current	32 A
[Us] Rated Supply Voltage	380...415 V AC 50/60 Hz
Earthing System	Compatible TT Compatible IT with additional isolation transformer on the power supply Compatible TN
Nominal Output Power	22 W 32 A
Socket Number	1

### Complementary

Connector Type	T2 vehicle end silver plated contacts Without connector charging station end
Range Compatibility	EVlink EVlink Wallbox EVH2 charging station
Standards	IEC 62196-1 IEC 62196-2
Product Certifications	CE
Length	4 m
Net Weight	3.1 kg

### Environment

Ip Degree Of Protection	IP54 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ambient Air Temperature For Operation	-30...50 °C
Ambient Air Temperature For Storage	-40...80 °C
Relative Humidity	5...95 %

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	15 cm
Package 1 Width	30 cm
Package 1 Length	40 cm
Package 1 Weight	2.484 kg

## Sustainability





**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>	
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>	
China Rohs Regulation	<a href="#">China RoHS declaration</a>	