

Product datasheet

Specifications



Galaxy VM Battery Breaker Box 630A EL

GVMBBB630EL

Overview

Presentation	Wall mounted battery breaker box for use with open battery rack configurations.
Lead Time	Usually Ships within 2 Weeks

Main

Main Input Voltage	400 V 3 phases
Battery Type	External battery system
Provided Equipment	Installation guide

Batteries & Runtime

Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Device Mounting	Open frame battery stands
Battery Power In Vah	0 VAh

Physical

Height	81 cm
Width	51.1 cm
Depth	29.1 cm
Net Weight	40 kg
Mounting Mode	Not rack-mountable

Conformance

Product Certifications	C-Tick CE RCM
Standards	EN/IEC 62040-2 EN/IEC 62040-3 IBC 2012 and CBC2013 to Sds=2.02g UL 1778 VFI-SS-111

Environmental

Ambient Air Temperature For Operation	0...40 °C
Operating Altitude	0...3333 ft
Relative Humidity	0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-25...65 °C
Storage Altitude	0.00...14999.82 m
Storage Relative Humidity	0...95 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	82 cm
Package 1 Width	30 cm
Package 1 Length	52 cm
Package 1 Weight	45 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
-------------------	--

China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	End of Life Information
---------------------	---