Product datasheet

Specifications





TeSys Deca contactor - 3P(3 NO) - AC-3 - <= 440 V 65 A - 36 V DC standard coil

LC1D65A3CD

() Discontinued on: 1 Jan 2008

() Discontinued

Main

Range	TeSys	
	TeSys Deca	
Range Of Product	TeSys Deca	
Product Or Component Type	Contactor	
Device Short Name	LC1D	
Contactor Application	Motor control	
	Resistive load	
Utilisation Category	AC-3	
	AC-1	
	AC-4	
Poles Description	3P	
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz	
	Power circuit: <= 300 V DC	
[le] Rated Operational Current	80 A (at <60 °C) at <= 440 V AC AC-1 for power circuit	
	65 A (at <60 $^{\circ}$ C) at <= 440 V AC AC-3 for power circuit	
[Uc] Control Circuit Voltage	36 V DC	

Complementary

Motor Power Kw	11 kW at 400 V AC 50/60 Hz (AC-4)	
	18.5 kW at 220230 V AC 50/60 Hz (AC-3)	
	30 kW at 380400 V AC 50/60 Hz (AC-3)	
Motor Power Hp	40 hp at 460/480 V AC 50/60 Hz for 3 phases motors	
	5 hp at 115 V AC 50/60 Hz for 1 phase motors	
	10 hp at 230/240 V AC 50/60 Hz for 1 phase motors	
	20 hp at 200/208 V AC 50/60 Hz for 3 phases motors	
	20 hp at 230/240 V AC 50/60 Hz for 3 phases motors	
	50 hp at 575/600 V AC 50/60 Hz for 3 phases motors	
Compatibility Code	LC1D	
Pole Contact Composition	3 NO	
Contact Compatibility	M4	
Protective Cover	With	
[Ith] Conventional Free Air	10 A (at 60 °C) for signalling circuit	
Thermal Current	80 A (at 60 °C) for power circuit	
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1	
	250 A DC for signalling circuit conforming to IEC 60947-5-1	
	1000 A at 440 V for power circuit conforming to IEC 60947	
Rated Breaking Capacity	1000 A at 440 V for power circuit conforming to IEC 60947	
Rated Breaking Capacity	1000 A at 440 V for power circuit conforming to IEC 60947	_

[Icw] Rated Short-Time Withstand Current	520 A 40 °C - 10 s for power circuit 900 A 40 °C - 1 s for power circuit
	110 A 40 °C - 10 min for power circuit
	260 A 40 °C - 1 min for power circuit 100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
	125 A gG at <= 690 V coordination type 1 for power circuit 125 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	1.5 mOhm - Ith 80 A 50 Hz for power circuit
Power Dissipation Per Pole	9.6 W AC-1 6.3 W AC-3
[Ui] Rated Insulation Voltage	Power circuit: 600 V CSA certified
	Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1
	Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V UL certified
	Power circuit: 690 V conforming to IEC 60947-4-1
Overvoltage Category	11
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	10 Mcycles
Electrical Durability	0.5 Mcycles 80 A AC-1 at Ue <= 440 V 1.45 Mcycles 65 A AC-3 at Ue <= 440 V
Control Circuit Type	DC standard
Coil Technology	Built-in bidirectional peak limiting diode suppressor
Control Circuit Voltage Limits	0.10.3 Uc (-4070 °C):drop-out DC
	0.751.25 Uc (-4060 °C):operational DC
	11.25 Uc (6070 °C):operational DC
Inrush Power In W	19 W (at 20 °C)
Hold-In Power Consumption In W	7.4 W at 20 °C
Operating Time	42.557.5 ms closing 1624 ms opening
Time Constant	34 ms
Maximum Operating Rate	3600 cyc/h 60 °C
Connections - Terminals	Power circuit: EverLink BTR screw connectors 1 135 mm ² - cable stiffness: flexible without cable end Power circuit: EverLink BTR screw connectors 2 125 mm ² - cable stiffness: flexible without cable end Power circuit: EverLink BTR screw connectors 1 135 mm ² - cable stiffness: flexible with cable end Power circuit: EverLink BTR screw connectors 2 125 mm ² - cable stiffness: flexible with cable end Power circuit: EverLink BTR screw connectors 1 135 mm ² - cable stiffness: flexible with cable end Power circuit: EverLink BTR screw connectors 1 135 mm ² - cable stiffness: solid without cable end Power circuit: EverLink BTR screw connectors 2 125 mm ² - cable stiffness: solid without cable end Power circuit: EverLink BTR screw connectors 2 125 mm ² - cable stiffness: solid without cable end Control circuit: spring terminals 1 2.5 mm ² - cable stiffness: flexible without cable end
	Control circuit: spring terminals 2 2.5 mm ² - cable stiffness: flexible without cable end

Tightening Torque	Power circuit: 8 N.m - on EverLink BTR screw connectors - cable 2535 mm ² hexagonal screw head 4 mm
	Power circuit: 5 N.m - on EverLink BTR screw connectors - cable 125 mm ² hexagonal screw head 4 mm
	Control circuit: 1.7 N.m - on EverLink BTR screw connectors - with screwdriver pozidriv No 2
	Power circuit: 2.5 N.m - on EverLink BTR screw connectors - with screwdriver pozidriv No 2
Auxiliary Contact Composition	1 NO + 1 NC
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Voltage	17 V for signalling circuit
Minimum Switching Current	5 mA for signalling circuit
Insulation Resistance	> 10 MOhm for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Mounting Support	Rail Plate

Environment

Standards	CSA C22.2 No 14
	EN 60947-4-1
	EN 60947-5-1
	IEC 60947-4-1
	IEC 60947-5-1
	UL 508
	IEC 60335-1
Product Certifications	000
	CSA
	UL
	GOST
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Protective Treatment	TH conforming to IEC 60068-2-30
Climatic Withstand	conforming to IACS E10 exposure to damp heat
	conforming to IEC 60947-1 Annex Q category D exposure to damp heat
Permissible Ambient Air	-4060 °C
Temperature Around The Device	6070 °C with derating
Operating Altitude	03000 m
Fire Resistance	850 °C conforming to IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz)
	Vibrations contactor closed (4 Gn, 5300 Hz)
	Shocks contactor closed (15 Gn for 11 ms)
	Shocks contactor open (10 Gn for 11 ms)
Height	122 mm
Width	55 mm
Depth	120 mm
Net Weight	0.935 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	6 cm	
Package 1 Width	14 cm	
Package 1 Length	15 cm	
Package 1 Weight	850 g	

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information