

Product datasheet

Specifications



Electronic overcurrent relay, TeSys LR97D, 24VAC/DC, 5 to 25A, 1C/O

LR97D25B

Main

Device Short Name	LR97
Product Or Component Type	Electronic overcurrent relay
Device Application	Protection
Relay Application	Overload $I_{max} > I_{setting}$ Locked rotor, mechanical jamming $I > 3 \times I_{setting}$ Sensitivity to phase failure
Product Compatibility	LC1D09...D38
Network Type	AC DC
[Us] Rated Supply Voltage	24 V AC/DC
Thermal Protection Adjustment Range	5...25 A
[Ue] Rated Operational Voltage	600 V AC 50/60 Hz for power circuit conforming to CSA 600 V AC 50/60 Hz for power circuit conforming to UL 690 V AC 50/60 Hz for power circuit conforming to IEC 60947-4-1
Quantity Per Set	Set of 10

Complementary

Network Frequency	50...60 Hz
Mounting Support	Direct on contactor Rail
Tripping Threshold	5...21 A
Surge Withstand	6 kV conforming to IEC 61000-4-5
Contacts Type And Composition	1 C/O
[Ith] Conventional Free Air Thermal Current	3 A for control circuit
Protection Type	BS fuse 3 A - for control circuit GB2 circuit breaker 3 A - for control circuit GG fuse 3 A - for control circuit
Maximum Power	28 W at 110 V DC conforming to IEC 60947 28 W at 220 V DC conforming to IEC 60947 55 W at 24 V DC conforming to IEC 60947 55 W at 48 V DC conforming to IEC 60947 140 VA at 48 V AC conforming to IEC 60947 360 VA at 110 V AC conforming to IEC 60947 360 VA at 220 V AC conforming to IEC 60947 70 VA at 24 V AC conforming to IEC 60947
[Ui] Rated Insulation Voltage	Power circuit: 600 V conforming to CSA Power circuit: 600 V conforming to UL Power circuit: 690 V conforming to IEC 60947-4-1
[Uimp] Rated Impulse Withstand Voltage	6 kV

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Phase Failure Sensitivity	< 3 s
Reset	Automatic reset 120 s fixed Electrical by interruption of power supply for minimum 0.1 s Manual reset
Time Range	0.2...10 s - O-time knob 0.3...10 s - O-time knob 0.5...30 s - D-time knob
Signalling Function	2 LEDs
Connections - Terminals	Control circuit: cable 1 x 1...25 mm²flexible with cable end Control circuit: cable 1 x 1...25 mm²flexible without cable end Power circuit: cable 1 x 1...4 mm²flexible with cable end Power circuit: cable 1 x 1.5...10 mm²flexible without cable end Power circuit: lug-clamp 1 x 1...4 mm²flexible with cable end Power circuit: lug-clamp 1 x 1.5...10 mm²flexible without cable end Control circuit: cable 2 x 1...25 mm²flexible with cable end Control circuit: cable 2 x 1...25 mm²flexible without cable end Control circuit: lug-clamp 1 x 1...25 mm²flexible with cable end Control circuit: lug-clamp 1 x 1...25 mm²flexible without cable end Control circuit: lug-clamp 2 x 1...25 mm²flexible with cable end Control circuit: lug-clamp 2 x 1...25 mm²flexible without cable end
Tightening Torque	Control circuit: 0.6...1.2 N.m on lug-clamp Power circuit: 2 N.m on cable
Height	67.5 mm
Width	45 mm
Depth	67.5 mm
Net Weight	0.172 kg

Environment

Standards	IEC 60947 IEC 60255-6
Product Certifications	UL GOST CSA
Protective Treatment	TH conforming to IEC 60068
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-25...60 °C conforming to IEC 60947-4-1
Ambient Air Temperature For Storage	-30...80 °C
Operating Altitude	2000 m
Fire Resistance	850 °C conforming to IEC 60695-2-1
Shock Resistance	15 gn 11 ms conforming to IEC 60068-2-7
Vibration Resistance	4 gn conforming to IEC 60068-2-6
Dielectric Strength	2 V 50 Hz conforming to IEC 60255-5
Resistance To Electrostatic Discharge	6 kV in indirect mode 8 kV in air
Resistance To Radiated Fields	10 V/m level 3
Resistance To Fast Transients	2 kV
Disturbance Radiated/Conducted	10 V conforming to EN 61000-4-6 Class A conforming to EN 55011

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Number Of Units In Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	7.7 cm
Package 1 Length	7.2 cm
Package 1 Weight	177.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	24
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.703 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	384
Package 3 Height	77.0 cm
Package 3 Width	80.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	83.748 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins