Product datasheet

Specifications





circuit breaker ComPact NSXm N (50 kA at 415 VAC), 4P 4d, 50 A rating Micrologic 4.1 trip unit, lugs and busbar connectors

LV426786

! Discontinued on: 13 Nov 2022

! End-of-service on: 26 Oct 2023

① Discontinued

Main

| Range | ComPact |
|--|--|
| Product Name | ComPact NSXm |
| Range Of Product | ComPact NSXm |
| Device Short Name | NSXm 50N |
| Product Or Component Type | Earth leakage circuit breaker |
| Device Application | Distribution Protection |
| Number Of Poles | 4P |
| Protected Poles Description | 4D |
| Neutral Position | Left |
| [In] Rated Current | 50 A at 40 °C |
| [Ue] Rated Operational Voltage | 440 V AC 50/60 Hz |
| Network Type | AC |
| Network Frequency | 50/60 Hz |
| Suitability For Isolation | Yes conforming to EN/IEC 60947-2 |
| Utilisation Category | Category A |
| [Icu] Rated Ultimate Short-Circuit Breaking Capacity | 90 kA Icu at 220240 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 380415 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 |
| Performance Level | N 50 kA 415 V AC |
| Trip Unit Name | MicroLogic 4.1 |
| Trip Unit Technology | Electronic |
| Trip Unit Protection Functions | LSoIR |
| Control Type | Toggle |
| Circuit Breaker Mounting Mode | By screws Clip-on |

Complementary

| [Ui] Rated Insulation Voltage | 500 V AC 50/60 Hz |
|--|-------------------|
| [Uimp] Rated Impulse Withstand Voltage | 8 kV |

| [Ics] Rated Service Short-Circuit Breaking Capacity | 90 kA at 220240 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 380415 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 |
|--|---|
| Mechanical Durability | 20000 cycles |
| Electrical Durability | 10000 cycles at 440 V In 20000 cycles at 440 V In/2 |
| Mounting Support | Plate DIN rail |
| Connection Terminals | compression lug/busbar |
| Connection Pitch | 35 mm with spreaders 27 mm without spreaders |
| 9 Mm Pitches | 12 module |
| Protection Type | L : for overload protection (thermal) So : for short time short-circuit protection with fixed delay I : for instantaneous short-circuit protection R : for earth-leakage protection |
| Trip Unit Rating | 50 A at 40 °C |
| Long-Time Pick-Up Adjustment Type Ir (Thermal Protection) | Adjustable 9 settings |
| [Ir] Long-Time Protection Pick-Up Adjustment Range | 2050 A |
| Long-Time Protection Delay Adjustment Type Tr | Fixed |
| [Tr] Long-Time Protection Delay Adjustment Range | 5 s at 7.2 x lr 8 s at 6 x lr 200 s at 1.5 x lr |
| Thermal Memory | 20 minutes before and after tripping |
| Short-Time Protection Pick-Up Adjustment Type Isd | Adjustable 9 settings |
| [Isd] Short-Time Protection Pick- Up Adjustment Range | 1.510 x lr |
| Short-Time Protection Delay Adjustment Type Tsd | Fixed |
| [Tsd] Short-Time Protection Delay Adjustment Range | 0.02 s |
| Instantaneous Protection Pick-Up Adjustment Type Ii | Fixed |
| [li] Instantaneous Protection Pick- Up Adjustment Range | 750 A |
| Earth-Leakage Protection | Integrated |
| Earth-Leakage Protection Sensitity Adjustment Type Iδn | Adjustable |
| [lδn] Earth-Leakage Protection Sensitivity Adjustment Range | 0.035 A |
| Earth-Leakage Sensitivity | 30 mA for class A 100 mA for class A 300 mA for class A 500 mA for class A 1000 mA for class A 1000 mA for class AC 100 mA for class AC 100 mA for class AC 300 mA for class AC 500 mA for class AC 1000 mA for class AC 500 mA for class AC 5000 mA for class AC |
| Earth-Leakage Protection Time Delay Adjustement Type ∆t | Adjustable |
| [∆t] Earth-Leakage Protection Time Delay Adjustment Range | 0 ms 60 ms 150 ms 500 ms 1000 ms |

| Neutral Protection Settings | No protection 1 x Ir |
|---|---|
| Number Of Slots For Electrical Auxiliaries | 1 slot(s) for auxiliary switch OF 1 slot(s) for alarm switch SD 1 slot(s) for voltage release MN or MX |
| Local Signalling | Flashing LED (green) for ready to operate LED 105 % Ir (red) for overload LED 90 % Ir (orange) for overload |
| Width (W) | 108 mm |
| Height (H) | 144 mm |
| Depth (D) | 80 mm |
| Net Weight | 1.63 kg |
| Colour | Grey (RAL 7016) |

Environment

| Standards | EN/IEC 60947 |
|---------------------------------------|---|
| Product Certifications | CCC EAC |
| Pollution Degree | 3 conforming to IEC 60664-1 |
| Ip Degree Of Protection | IP40 conforming to IEC 60529 |
| Ik Degree Of Protection | IK07 conforming to IEC 62262 |
| Ambient Air Temperature For Operation | -2570 °C |
| Ambient Air Temperature For Storage | -4085 °C |
| Relative Humidity | 095 % |
| Operating Altitude | 02000 m without derating 20005000 m with derating |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 15.3 cm |
| Package 1 Width | 13.4 cm |
| Package 1 Length | 19 cm |
| Package 1 Weight | 1.682 kg |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 4 |
| Package 2 Height | 30 cm |
| Package 2 Width | 30 cm |
| Package 2 Length | 40 cm |
| Package 2 Weight | 6.728 kg |

Sustainability Green Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |