Product datasheet





Circuit breaker basic frame, ComPact NSX100N, 50kA at 415VAC 50/60 Hz, 100A, without trip unit, 4 poles

LV429011

! Discontinued on: 31 Dec 2023

! Discontinued

Main	
Range	ComPact
Range Of Product	ComPact NSX100250
Device Short Name	NSX100N
Product Or Component Type	Basic frame
Device Application	Distribution
Circuit Breaker Name	Compact NSX100N
Number Of Poles	4P
Neutral Position	Left
[In] Rated Current	100 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	10 kA at 600 V AC 50/60 Hz conforming to UL 508 85 kA at 240 V AC 50/60 Hz conforming to UL 508 10 kA lcu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 35 kA lcu at 525 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 480 V AC 50/60 Hz conforming to UL 508 36 kA lcu at 500 V AC 50/60 Hz conforming to IEC 60947-2 50 kA lcu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 50 kA lcu at 440 V AC 50/60 Hz conforming to IEC 60947-2 90 kA lcu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	N 50 kA 415 V AC
Control Type	Toggle
Mounting Mode	Fixed

Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	10 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 35 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 36 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 90 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2

Life Is On Schneider 25 Apr 2024

Mechanical Durability	50000 cycles conforming to IEC 60947-2
Electrical Durability	10000 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 20000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 30000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 50000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	35 mm
Protection Type	Without protection
Width (W)	140 mm
Height (H)	161 mm
Depth (D)	86 mm

Environment

Standards	EN/IEC 60947-2 UL 508
Product Certifications	CSA UL
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.8 cm
Package 1 Width	14.7 cm
Package 1 Length	19 cm
Package 1 Weight	1.89 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	11
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	21.545 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information