Product datasheet

Specification





logic controller, Modicon M241, 24 IO, transistor, PNP

TM241C24T

Main

Range Of Product	Modicon M241	
Product Or Component Type	Logic controller	
[Us] Rated Supply Voltage	24 V DC	
Discrete Input Number	14, discrete input 8 fast input conforming to IEC 61131-2 Type 1	
Discrete Output Type	Transistor	
Discrete Output Number	10 transistor 4 fast output	
Discrete Output Voltage	24 V DC for transistor output	
Discrete Output Current	0.5 A for transistor output (Q0Q9) 0.1 A for fast output (PTO mode) (Q0Q3)	

Complementary

Discrete I/O Number	24
Maximum Number Of I/O Expansion Module	7 (local I/O-Architecture) 14 (remote I/O-Architecture)
Supply Voltage Limits	20.428.8 V
Inrush Current	50 A
Power Consumption In W	32.640.4 W (with max number of I/O expansion module)
Discrete Input Logic	Sink or source
Discrete Input Voltage	24 V
Discrete Input Voltage Type	DC
Voltage State 1 Guaranteed	>= 15 V for input
Voltage State 0 Guaranteed	<= 5 V for input
Discrete Input Current	5 mA for input 10.7 mA for fast input
Input Impedance	4.7 kOhm for input 2.81 kOhm for fast input
Response Time	50 μs turn-on, I0I13 terminal(s) for input 50 μs turn-off, I0I13 terminal(s) for input <= 2 μs turn-on, I0I7 terminal(s) for fast input <= 2 μs turn-off, I0I7 terminal(s) for fast input <= 34 μs turn-on, Q0Q9 terminal(s) for output <= 250 μs turn-off, Q0Q9 terminal(s) for output <= 2 μs turn-on, Q0Q3 terminal(s) for fast output

<= 2 µs turn-off, Q0...Q3 terminal(s) for fast output

Configurable Filtering Time	1 µs for fast input 12 ms for fast input 0 ms for input 1 ms for input 4 ms for input 12 ms for input
Discrete Output Logic	Positive logic (source)
Output Voltage Limits	30 V DC
Maximum Current Per Output Common	2 A with Q0Q3 for fast output 2 A with Q4Q7 for output 1 A with Q8Q9 for output
Maximum Output Frequency	20 kHz for fast output (PWM mode) 100 kHz for fast output (PLS mode) 1 kHz for output
Accuracy	+/- 0.1 % at 0.020.1 kHz for fast output +/- 1 % at 0.11 kHz for fast output
Maximum Leakage Current	5 μA for output
Maximum Voltage Drop	<1 V
Maximum Tungsten Load	<2.4 W
Protection Type	Short-circuit protection Short-circuit and overload protection with automatic reset Reverse polarity protection for fast output
Reset Time	10 ms automatic reset output 12 s automatic reset fast output
Memory Capacity	64 MB for system memory RAM
Data Backed Up	128 MB built-in flash memory for backup of user programs
Data Storage Equipment	<= 16 GB SD card (optional)
Battery Type	BR2032 lithium non-rechargeable, battery life: 4 year(s)
Backup Time	2 years at 25 °C
Execution Time For 1 Kinstruction	0.3 ms for event and periodic task 0.7 ms for other instruction
Application Structure	4 cyclic master tasks 3 cyclic master tasks + 1 freewheeling task 8 external event tasks 8 event tasks
Realtime Clock	With
Clock Drift	<= 60 s/month at 25 °C
Positioning Functions	PTO function 4 channel(s) (positioning frequency: 100 kHz) PTO function 4 channel(s) for transistor output (positioning frequency: 1 kHz)
Counting Input Number	4 fast input (HSC mode) at 200 kHz 14 standard input at 1 kHz
Control Signal Type	A/B at 100 kHz for fast input (HSC mode) Pulse/direction at 200 kHz for fast input (HSC mode) Single phase at 200 kHz for fast input (HSC mode)
Integrated Connection Type	Non isolated serial link serial 1 with RJ45 connector and RS232/RS485 interface Non isolated serial link serial 2 with removable screw terminal block connector and RS485 interface USB port with mini B USB 2.0 connector
Supply	(serial 1)serial link supply: 5 V, <200 mA
Transmission Rate	1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 480 Mbit/s for bus length of 3 m for USB
Communication Port Protocol	Non isolated serial link: Modbus master/slave

1 LED (green) for PWR
1 LED (green) for RUN
1 LED (red) for module error (ERR) 1 LED (red) for I/O error (I/O)
1 LED (green) for SD card access (SD)
1 LED (red) for BAT
1 LED (green) for SL1
1 LED (green) for SL2
1 LED (red) for bus fault on TM4 (TM4) 1 LED per channel (green) for I/O state
removable screw terminal blockfor inputs and outputs (pitch 5.08 mm)
removable screw terminal blockfor connecting the 24 V DC power supply (pitch 5.08 mm)
Unshielded cable: <50 m for input
Shielded cable: <10 m for fast input Unshielded cable: <50 m for output
Shielded cable: <3 m for fast output
Between supply and internal logic at 500 V AC
Non-insulated between supply and ground
Between input and internal logic at 500 V AC
Non-insulated between inputs Between fast input and internal logic at 500 V AC
Between fast input and internal logic at 500 V AC Between output and internal logic at 500 V AC
Non-insulated between outputs
Between fast output and internal logic at 500 V AC
CE
1 kV power lines (DC) common mode conforming to IEC 61000-4-5
1 kV shielded cable common mode conforming to IEC 61000-4-5
0.5 kV power lines (DC) differential mode conforming to IEC 61000-4-5
1 kV relay output differential mode conforming to IEC 61000-4-5 1 kV input common mode conforming to IEC 61000-4-5
1 kV transistor output common mode conforming to IEC 61000-4-5
Top hat type TH35-15 rail conforming to IEC 60715
Top hat type TH35-7.5 rail conforming to IEC 60715
plate or panel with fixing kit
90 mm
95 mm
150 mm
0.53 kg
ANSI/ISA 12-12-01
CSA C22.2 No 142
CSA C22.2 No 213
IEC 61131-2:2007
Marine specification (LR, ABS, DNV, GL) UL 508
RCM
cULus
CE
UKCA
DNV-GL ABS
ABS LR
8 kV in air conforming to IEC 61000-4-2
4 kV on contact conforming to IEC 61000-4-2
10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3
3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3
1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3

2 kV (power lines) conforming to IEC 61000-4-4 1 kV (serial link) conforming to IEC 61000-4-4 1 kV (input) conforming to IEC 61000-4-4 1 kV (transistor output) conforming to IEC 61000-4-4

Resistance To Fast Transients

Resistance To Conducted Disturbances	10 V 0.1580 MHz conforming to IEC 61000-4-6 3 V 0.180 MHz conforming to Marine specification (LR, ABS, DNV, GL) 10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to
Electromagnetic Emission	Marine specification (LR, ABS, DNV, GL) Conducted emissions - test level: 12069 dBμV/m QP (power lines) at 10150 kHz conforming to IEC 55011 Conducted emissions - test level: 63 dBμV/m QP (power lines) at 1.530 MHz conforming to IEC 55011 Radiated emissions - test level: 40 dBμV/m QP class A at 30230 MHz conforming to IEC 55011 Conducted emissions - test level: 7963 dBμV/m QP (power lines) at 1501500 kHz conforming to IEC 55011 Radiated emissions - test level: 47 dBμV/m QP class A at 2301000 MHz conforming to IEC 55011
Immunity To Microbreaks	10 ms
Ambient Air Temperature For Operation	-1050 °C (vertical installation) -1055 °C (horizontal installation)
Ambient Air Temperature For Storage	-2570 °C
Relative Humidity	1095 %, without condensation (in operation) 1095 %, without condensation (in storage)
Ip Degree Of Protection	IP20 with protective cover in place
Pollution Degree	2
Operating Altitude	02000 m
Storage Altitude	03000 m
Vibration Resistance	3.5 mm at 58.4 Hz on symmetrical rail 3 gn at 8.4150 Hz on symmetrical rail 3.5 mm at 58.4 Hz on panel mounting 3 gn at 8.4150 Hz on panel mounting
Shock Resistance	15 gn for 11 ms
Packing Units	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Unit Type Of Package 1 PCE Number Of Units In Package 1 Package 1 Height 11.367 cm Package 1 Width 13.104 cm Package 1 Length 18.744 cm Package 1 Weight 640.0 g Unit Type Of Package 2 S03 Number Of Units In Package 2 8 Package 2 Height 30 cm Package 2 Width 30 cm Package 2 Length 40 cm Package 2 Length 5.99 kg Unit Type Of Package 3 Po6 Number Of Units In Package 3 Package 3 Height 75.0 cm Package 3 Width 60.0 cm Package 3 Length 80.0 cm	
Package 1 Height 11.367 cm Package 1 Width 13.104 cm Package 1 Length 18.744 cm Package 1 Weight 640.0 g Unit Type Of Package 2 S03 Number Of Units In Package 2 8 Package 2 Height 30 cm Package 2 Width 30 cm Package 2 Length 40 cm Package 2 Weight 5.99 kg Unit Type Of Package 3 P06 Number Of Units In Package 3 64 Package 3 Height 75.0 cm Package 3 Width 60.0 cm	t Type Of Package 1
Package 1 Width 13.104 cm Package 1 Length 18.744 cm Package 1 Weight 640.0 g Unit Type Of Package 2 S03 Number Of Units In Package 2 8 Package 2 Height 30 cm Package 2 Width 30 cm Package 2 Length 40 cm Package 2 Weight 5.99 kg Unit Type Of Package 3 P06 Number Of Units In Package 3 64 Package 3 Height 75.0 cm Package 3 Width 60.0 cm	nber Of Units In Package 1
Package 1 Length 18.744 cm Package 1 Weight 640.0 g Unit Type Of Package 2 S03 Number Of Units In Package 2 Package 2 Height 30 cm Package 2 Width 30 cm Package 2 Length 40 cm Package 2 Weight 5.99 kg Unit Type Of Package 3 Po6 Number Of Units In Package 3 64 Package 3 Height 75.0 cm Package 3 Width 60.0 cm	kage 1 Height
Package 1 Weight 640.0 g Unit Type Of Package 2 S03 Number Of Units In Package 2 8 Package 2 Height 30 cm Package 2 Width 30 cm Package 2 Length 40 cm Package 2 Weight 5.99 kg Unit Type Of Package 3 P06 Number Of Units In Package 3 64 Package 3 Height 75.0 cm Package 3 Width 60.0 cm	 kage 1 Width
Unit Type Of Package 2 S03 Number Of Units In Package 2 8 Package 2 Height 30 cm Package 2 Width 30 cm Package 2 Length 40 cm Package 2 Weight 5.99 kg Unit Type Of Package 3 P06 Number Of Units In Package 3 64 Package 3 Height 75.0 cm Package 3 Width 60.0 cm	kage 1 Length
Number Of Units In Package 2 8 Package 2 Height 30 cm Package 2 Width 30 cm Package 2 Length 40 cm Package 2 Weight 5.99 kg Unit Type Of Package 3 P06 Number Of Units In Package 3 64 Package 3 Height 75.0 cm Package 3 Width 60.0 cm	kage 1 Weight
Package 2 Height 30 cm Package 2 Width 30 cm Package 2 Length 40 cm Package 2 Weight 5.99 kg Unit Type Of Package 3 P06 Number Of Units In Package 3 64 Package 3 Height 75.0 cm Package 3 Width 60.0 cm	t Type Of Package 2
Package 2 Width 30 cm Package 2 Length 40 cm Package 2 Weight 5.99 kg Unit Type Of Package 3 P06 Number Of Units In Package 3 64 Package 3 Height 75.0 cm Package 3 Width 60.0 cm	nber Of Units In Package 2
Package 2 Length 40 cm Package 2 Weight 5.99 kg Unit Type Of Package 3 P06 Number Of Units In Package 3 64 Package 3 Height 75.0 cm Package 3 Width 60.0 cm	kage 2 Height
Package 2 Weight 5.99 kg Unit Type Of Package 3 P06 Number Of Units In Package 3 64 Package 3 Height 75.0 cm Package 3 Width 60.0 cm	kage 2 Width
Unit Type Of Package 3 P06 Number Of Units In Package 3 64 Package 3 Height 75.0 cm Package 3 Width 60.0 cm	 kage 2 Length
Number Of Units In Package 3 64 Package 3 Height 75.0 cm Package 3 Width 60.0 cm	kage 2 Weight
Package 3 Height 75.0 cm Package 3 Width 60.0 cm	t Type Of Package 3
Package 3 Width 60.0 cm	nber Of Units In Package 3
	kage 3 Height
Package 3 Length 90.0 cm	kage 3 Width
out offi	ckage 3 Length
Package 3 Weight 56 kg	 kage 3 Weight



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
	Rohs Exemption Information	Yes
②	Pvc Free	

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information


Product datasheet

TM241C24T

Dimensions Drawings

Dimensions







TM241C24T


Mounting and Clearance


Clearance






Mounting Position







Acceptable Mounting



NOTE: Expansion modules must be mounted above the logic controller.

Incorrect Mounting








Direct Mounting On a Panel Surface


Mounting Hole Layout




Connections and Schema

Digital Inputs

Wiring Diagram





(*): Type T fuse

(1): The COM0, COM1 and COM2 terminals are not connected internally

(A): Sink wiring (positive logic)


(B): Source wiring (negative logic)

Fast Input Wiring (I0...I7)



Fast Transistor Outputs


Wiring Diagram



(*): 2 A fast-blow fuse

Transistor Outputs

Wiring Diagram



(*): Type T fuse

(1): The V1+ and V2+ terminals are not connected internally.

(2): The V1- and V2- terminals are not connected internally.

USB Mini-B Connection

25 Apr 2024

