Product datasheet

Specifications





Harmony Electromechanical Relays, Slim interface relay pre assembled, 6A, 1CO, with LED, screw connectors, 12V AC DC

RSL1PVJU

Main

Range Of Product	Harmony Electromechanical Relays
Series Name	Interface relay
Product Or Component Type	Pre-assembled plug-in relay with socket
Device Short Name	RSL
Contacts Type And Composition	1 C/O
Contact Operation	Standard
[Uc] Control Circuit Voltage	12 V AC/DC
[Ithe] Conventional Enclosed Thermal Current	6 A at -4055 °C
Status Led	With
Shape Of Pin	Flat (PCB type)

Complementary

oompromontal y	
Fixing Mode	Plastic compression spring
Average Resistance	848 Ohm network: DC at 23 °C +/- 10 %
[Ui] Rated Insulation Voltage	250 V conforming to IEC 277 V conforming to cUL
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC
Contacts Material	Silver alloy (AgSnO2)
[Ie] Rated Operational Current	6 A 1 C/O (AC-1/DC-1) conforming to IEC/UL
Minimum Switching Current	100 mA
Maximum Switching Voltage	277 V
Minimum Switching Voltage	12 V
Maximum Switching Capacity	1500 VA 150 W
Minimum Switching Capacity	120 mW
Operating Rate	<= 72000 cycles/hour no-load <= 360 cycles/hour under load
Mechanical Durability	1000000 cycles
Electrical Durability	60000 cycles for resistive load, 6 A at 250 V, AC-1
Operating Time	5 ms reset 12 ms
Marking	CE
Protection Category	RT III

Level A group mounting
Any position
78.6 mm
6.2 mm
95 mm
(11-12-14)OC (A1-A2)CO
10
0.029 kg
6 A at 250 V AC 0.5 mm mounting distance
0.17 W, DC
>= 0.05 Uc
Separate
Screw connectors, 1 x 0.21 x 2.5 mm ² (AWG 24AWG 14) flexible with cable end Screw connectors, 1 x 0.21 x 2.5 mm ² (AWG 24AWG 14) solid without cable end
< 0.5 N.m for M2.5 screw(s)
B10d = 60000
Without push-button
35 mm symmetrical DIN rail
Complete product

Environment

12 V AC/DC (input voltage limit: 11.414.4 V)
1000 V AC between contacts
4000 V AC between coil and contact
CSA C22.2 No 14
UL 508
IEC 61810-1
UL
GOST
CSA
-4085 °C
10 gn, amplitude = +/- 1 mm (f = 10…150 Hz)10 cycles not operating conforming to IEC 60068-2-6
5 gn, amplitude = +/- 1 mm (f = 10150 Hz)10 cycles in operation conforming to IEC 60068-2-6
IP40 conforming to IEC 60529
10 gn (duration = 11 ms) for in operation conforming to IEC 60068-2-27
5 gn (duration = 11 ms) for not operating conforming to IEC 60068-2-27
-4055 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.7 cm
Package 1 Width	8 cm

Package 1 Length	9.7 cm
Package 1 Weight	28 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	7 cm
Package 2 Width	10.3 cm
Package 2 Length	8.5 cm
Package 2 Weight	314 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	300
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	9.903 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Toxic Free
Phenolic Free Solution

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Product datasheet

Dimensions Drawings

Dimensions

