



# Interface plug-in relay, 10 A, 1 CO, clear cover, 48 V AC

RXG15E7

- ! Discontinued on: 10 June 2015
- ! End-of-service on: 21 Oct 2020

① Discontinued

#### Main

Range Of Product	Harmony Relay
Series Name	Interface relay
Product Or Component Type	Plug-in relay
Device Short Name	RXG
Contacts Type And Composition	1 C/O
[Ithe] Conventional Enclosed Thermal Current	10 A at -4055 °C

# Complementary

[le] Rated Operational Current	10 A at 30 V (DC) conforming to UL 10 A at 30 V (DC) conforming to IEC 10 A at 250 V (AC) conforming to IEC 10 A at 250 V (AC) conforming to UL
Electrical Durability	100000 cycles for NO resistive load at 55 °C 100000 cycles for NC resistive load at 55 °C
Coil Resistance	1100 Ohm +/- 10 %
Shock Resistance	20 gn in operation 100 gn not in operation
Mounting Position	Any position
Average Consumption In Va	0.82 VA 60 Hz
Control Circuit Voltage Limits	0.81.1 Uc AC
[Uc] Control Circuit Voltage	48 V AC 50/60 Hz
Colour Of Cover	Transparent
Drop-Out Voltage Threshold	>= 0.3 Uc AC
Load Current	10 A at 250 V AC
Minimum Switching Capacity	500 mW at 100 mA, 5 V DC
Maximum Switching Capacity	2500 VA
Torque Value	0.8 N.m
Insulation Resistance	1000 MOhm at 500 V DC
Mechanical Durability	10000000 cycles
Safety Reliability Data	B10d = 100000
Overvoltage Category	III
Maximum Switching Voltage	250 V AC 30 V DC

Protection Category	RTI
Operating Rate	<= 1800 cycles/hour under load <= 18000 cycles/hour no-load
Utilisation Coefficient	20 %
Pollution Degree	2
[Ui] Rated Insulation Voltage	250 V conforming to IEC 300 V conforming to CSA 300 V conforming to UL
Dielectric Strength	1000 V AC between contacts with micro disconnection 5000 V AC between coil and contact with reinforced insulation
Test Levels	Level A group mounting
Device Presentation	Complete product
Contacts Material	Silver alloy (AgSnO2ln2O3)
Net Weight	0.019 kg
Environment	

Standards	CSA C22.2 No 14 IEC 61810-1 UL 508	
Product Certifications	EAC CSA UL CE DNV-GL	
Ambient Air Temperature For Storage	-4085 °C	
Ambient Air Temperature For Operation	-4070 °C	
Ip Degree Of Protection	IP40	
Relative Humidity	1085 %	
Vibration Resistance	3 gn, amplitude = +/- 0.75 mm (f = 10150 Hz)in operation 5 gn, amplitude = +/- 0.75 mm (f = 10150 Hz)not in operation	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>9</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes


#### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations


# **RXG15E7**

#### **Dimensions Drawings**

#### **Dimensions**








# **RXG15E7**

Connections and Schema


#### Wiring Diagram



#### Performance Curves

#### **Performance Curves**

#### **Maximum Switching Capacity**



X: Switching voltage (V)

Y: Switching current (A)

(1) AC Resistive Load


(2) AC Inductive Load cos(Ø)=0.4

(3) DC Resistive Load

(4) DC Inductive Load (L/R=7ms)

#### Life Expectancy

Resistive Load



X: Contact Current (A)


Y: Operating Cycle Number

#### Life Expectancy

Inductive Load

# **Product datasheet**


### **RXG15E7**



- X : Contact Current (A)
  Y : Operating Cycle Number
- **NOTE:** These are typical curves, actual durability depends on load, environment, duty cycle, etc.

#### **Coil Operating Range**

#### **AC Coil Operating Range VS Ambient Temperature**



- X : Ambient temperature (°C)
- Y: Coil voltage (U/Uc)
- (1) Permitted operating range area