

Product datasheet

Specifications



Line-Voltage Fan Coil Room Controller: BACnet MS/TP, ZigBee Embedded, RH sensor & control, IP ready, PIR motion sensor, White Case/Fascia

SER8350A5B11P

Main

Product Name	SE8000 Series
Device Short Name	SER8300
Product Or Component Type	Room controller
Device Application	Line voltage fan coil
Net Weight	340 g
Awg Gauge	AWG 24...AWG 18
Height	120 mm
Width	86 mm
Directives	2014/30/EU - electromagnetic compatibility 2014/35/EU - low voltage directive 2014/53/EU - radio equipment directive
[In] Rated Current	4 A
Depth	25 mm
Ambient Air Temperature For Operation	0...50 °C
Market Segment	Lodging Small commercial Hotel Buildings Healthcare Non-critical buildings Office Residential School
Housing Colour	White
Ambient Air Temperature For Storage	-30...50 °C
Measurement Accuracy	Temperature: +/- 0.5 °C, Humidity: +/- 5 %, 20...80 % RH (non-condensing) Humidity: +/- 10 %, 10...20 % (non-condensing) Humidity: +/- 10 %, 80...90 % (non-condensing)
Information Displayed	Temperature: - 40...122 °F
Network Frequency	50 Hz 60 Hz
Communication Port Protocol	BACnet MS/TP Modbus RTU Zigbee Pro
Temperature Setting Range	12...37.5 °C cooling 4.5...32 °C heating
Input Voltage	0...10 V DC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Output Voltage	24 V AC for relay output 0...10 V DC for analog output
Relative Humidity	0...95 %
Output Current	1 A relay output 3 A relay output (inrush)
Input Type	2 x dry contact 5 x analog
Sensor Type	10 kOhm T2 NTC thermistor temperature Space RH sensor humidity
Output Type	5 xrelay output 4 xuniversal
[Us] Rated Supply Voltage	7 V DC 50/60 Hz +/- 10 %
Standards	EN/IEC 60730-1 EN/IEC 60730-2-9 EN/IEC 60730-2-13 CSA E60730-2-9 UL 60730-2-9 UL 60730-2-13 ICES-003 FCC part 15 Subpart B ETSI EN 300 328:v2.1.1 ETSI EN 301 489-1:v1.9.2 FCC part 15 Subpart C ETSI EN 301 489-17:v2.2.1, 2012 RSS 247
Humidity Setting Range	30...95 %
Range	EcoStruxure Building Expert
Economizer	No
Humidity Control	Yes
Pir Cover	Yes
Scheduling	Yes

Complementary

Surface Finish	Matt
Surface Treatment	Untreated
Function Available	Fan control HVAC control Available with CO2/RH/T Brightness sensor Changes can be made directly over display Code lock function Easily configurable Firmware update by USB

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	12.0 cm
Package 1 Length	2.5 cm
Package 1 Weight	245.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration