Product datasheet

Specifications





Light block, Harmony XB4, Harmony XB5, flashing, for head 22mm, universal LED, screw clamp terminals, 240V

ZBV18M1

Main

| Range Of Product | Harmony XB4 Harmony XB5 |
|-------------------------------|--|
| Product Or Component Type | Light block |
| Device Short Name | ZBV |
| Sale Per Indivisible Quantity | 5 |
| Connections - Terminals | Screw clamp terminals, <= 2 x 1.5 mm ² with cable end conforming to IEC 60947-1 Screw clamp terminals, >= 1 x 0.22 mm ² without cable end conforming to IEC 60947-1 |
| Signalling Type | Flashing |
| Light Source | Universal LED |
| Bulb Base | Integral LED |
| Light Block Supply | Direct |
| Light Source Colour | White |
| [Us] Rated Supply Voltage | 230240 V AC at 50/60 Hz |

Complementary

| Net Weight | 0.017 kg |
|-----------------------------|---|
| Tightening Torque | 0.81.2 N.m conforming to IEC 60947-1 |
| Shape Of Screw Head | Cross compatible with Philips no 1 screwdriver |
| | Cross compatible with pozidriv No 1 screwdriver |
| | Slotted compatible with flat Ø 4 mm screwdriver |
| | Slotted compatible with flat Ø 5.5 mm screwdriver |
| Supply Voltage Limits | 195264 V AC |
| Current Consumption | 14 mA |
| Service Life | 100000 h at rated voltage and 25 °C |
| Surge Withstand | 1 kV conforming to IEC 61000-4-5 |
| Mounting Of Block | Front mounting |
| Electrical Composition Code | M1 |
| | M2 |
| | M3 |
| | M4 |
| | M5 |
| | M6 |
| | M10 |
| | MF1 |
| | P1 |
| | P2 |
| | PF1 |

Environment

| Protective Treatment | тн |
|--|--|
| Ambient Air Temperature For Storage | -4070 °C |
| Ambient Air Temperature For Operation | -4070 °C |
| Ip Degree Of Protection | IP20 conforming to IEC 60529 |
| Standards | UL 508 IEC 60947-5-5 IEC 60947-1 CSA C22.2 No 14 IEC 60947-5-4 IEC 60947-5-1 JIS C8201-5-1 JIS C8201-1 |
| Product Certifications | UL listed CSA |
| Resistance To Fast Transients | 2 kV conforming to IEC 61000-4-4 |
| Resistance To Electromagnetic Fields | 10 V/m conforming to IEC 61000-4-3 |
| Resistance To Electrostatic Discharge | 6 kV on contact (on metal parts) conforming to IEC 61000-4-2 8 kV in free air (in insulating parts) conforming to IEC 61000-4-2 |
| Electromagnetic Emission | Class B conforming to IEC 55011 |
| [Us] Rated Supply Voltage | 240 V |

Packing Units

| - | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.000 cm |
| Package 1 Width | 3.500 cm |
| Package 1 Length | 4.000 cm |
| Package 1 Weight | 9.000 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 5 |
| Package 2 Height | 4.500 cm |
| Package 2 Width | 5.000 cm |
| Package 2 Length | 5.500 cm |
| Package 2 Weight | 51.000 g |
| Unit Type Of Package 3 | S02 |
| Number Of Units In Package 3 | 250 |
| Package 3 Height | 15.000 cm |
| Package 3 Width | 30.000 cm |
| Package 3 Length | 40.000 cm |
| Package 3 Weight | 2.794 kg |
| | |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |