

Product data sheet

Specifications



Switch, reversing drum, 5 HP at 575 VAC single phase, 7.5 HP at 575 VAC polyphase, handle operated, NEMA 1 enclosure

2601BG1

Main

Product	Reversing Drum Switch
Enclosure Rating	NEMA 1
Horsepower	1.5 hp 115 V AC, 1 phase 3 hp 230 V AC, 1 phase 5 hp 460 V AC, 1 phase 5 hp 575 V AC, 1 phase 5 hp 200 V AC, 3 phases 5 hp 230 V AC, 3 phases 7.5 hp 460 V AC, 3 phases 7.5 hp 575 V AC, 3 phases 2 hp 115 V DC 2 hp 230 V DC
Maximum Rated Voltage	600 V AC 250 V DC
Number Of Poles	3P

Complementary

Certifications	UL listed CSA
Electrical Connection	Screw-clamp terminals
Type	B
Width	2.68 in (68.07 mm)
Height	5.38 in (136.65 mm)
Depth	4.61 in (117.09 mm)
Product Weight	1.34 lb(US) (0.61 kg)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.69 in (11.9 cm)
Package 1 Width	5.59 in (14.2 cm)
Package 1 Length	7.09 in (18.0 cm)
Package 1 Weight	2.25 lb(US) (1.02 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Reach Regulation	REACH Declaration
Eu Rohs Directive	Not compliant
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information

Dimensions Drawings

Approximate Dimensions



Connections and Schema

Connections and Wiring Diagrams

