

Product data sheet

Specifications



Multi9 - C60 UL489 - MCB - 1P - 13 A - D Curve - 120 V - 10 kA - ring term

60228

 **Discontinued on:** Jan 28, 2021

 **Discontinued**

Main

Range	Multi9
Product Name	Multi9 C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60 UL489
Device Application	Distribution
Poles Description	1P
Number Of Protected Poles	1
[In] Rated Current	13 A 77 °F (25 °C)
Network Type	AC DC
Trip Unit Technology	Thermal-magnetic
Curve Code	D
Breaking Capacity	5 kA AIR 240 V AC UL 489 10 kA Icu 240 V AC EN/IEC 60947-2 10 kA Icu 240 V AC GB 14048.2 10 kA Icu 60 V DC EN/IEC 60947-2 10 kA Icu 60 V DC GB 14048.2 10 kA AIR 120 V AC UL 489 10 kA AIR 60 V DC UL 489 10 kA AIR 120 V AC CSA C22.2 No 5.2 5 kA AIR 240 V AC CSA C22.2 No 5.2 10 kA AIR 60 V DC CSA C22.2 No 5.2
Suitability For Isolation	Yes EN/IEC 60947-2

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	240 V AC 60 V DC 120 V AC
Magnetic Tripping Limit	12 x In +/- 20 % AC 17 x In +/- 20 % DC
Limitation Class	3 EN/IEC 60947-2
[Ui] Rated Insulation Voltage	500 V AC EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kVEN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	2
Height	4.84 in (123 mm)
Width	0.71 in (18 mm)
Depth	2.87 in (73 mm)
Net Weight	0.24 lb(US) (0.11 kg)
Colour	Grey
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Provision For Padlocking	Padlockable
Connections - Terminals	Ring terminal top or bottom)
Tightening Torque	17.70 lbf.in (2 N.m) top or bottom

Environment

Standards	GB 14048.2 EN/IEC 60947-2 UL 489 CSA C22.2 No 5
Product Certifications	CSA CCC IEC UL
Ip Degree Of Protection	IP40 (modular enclosure) conforming to IEC 60529 IP10 conforming to IEC 60529
Pollution Degree	3 EN/IEC 60947-2
Overvoltage Category	IV
Tropicalisation	2 IEC 60068-1
Relative Humidity	95 % 131 °F (55 °C)
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-22...158 °F (-30...70 °C)
Ambient Air Temperature For Storage	-40...176 °F (-40...80 °C)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.95 in (7.5 cm)
Package 1 Width	0.71 in (1.8 cm)
Package 1 Length	0.49 in (1.24 cm)
Package 1 Weight	0.29 lb(US) (0.133 kg)

Contractual warranty

Warranty	18 months
----------	-----------