Product data sheet

Specifications







Transformer, dry type, 45kVA, 3 phase, 208V delta primary, 480Y/277V secondary, 18D, 150C rise

EE45T212H

Main

| Product | Energy Efficient Transformer |
|------------------------|------------------------------|
| Enclosure Code | 18D |
| Enclosure Type | NEMA 2 |
| Insulation Temperature | 428 °F (220 °C) |
| Phase | 3 phases |
| Primary Voltage | 208 V delta |
| Power Rating | 45 kVA |
| Secondary Voltage | 480Y/277 V |
| Full Capacity Taps | 3 5 % 1+ 2- |
| Temperature Rise | 150 °C |
| Winding Material | Aluminium |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----|
| Number Of Units In Package 1 | 1 |

Contractual warranty

| Warranty | 18 months | |
|----------|-----------|--|
|----------|-----------|--|



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| ② | Toxic Heavy Metal Free | |
| ② | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Eu Rohs Directive | Compliant |
|--------------------------|---|
| | EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |

Dimensions Drawings

Approximate Dimensions

