

# Product data sheet

Specifications



## COMBO STARTER 600VAC 18A NEMA

8538SBG11V81CF4TX10

### Main

|                      |                             |
|----------------------|-----------------------------|
| Product              | Combination Starter         |
| Type                 | S                           |
| Control Circuit Type | Control circuit transformer |

### Complementary

|                         |  |
|-------------------------|--|
| Control Circuit Voltage | 120 V AC 60 Hz secondary circuit<br>480 V AC 60 Hz primary circuit                                       |
| Starter Type            | Non reversing  |
| Number Of Poles         | 3P   |
| Horsepower Rating       | 3 hp 200 V AC, 3 phases<br>3 hp 230 V AC, 3 phases<br>5 hp 460 V AC, 3 phases<br>5 hp 575 V AC, 3 phases |
| Maximum Voltage Rating  | 600 V AC   |
| Control Units           | Selector switch HAND-OFF-AUTO)   |
| Pilot Light             | No indicator   |
| Auxiliary Contacts      | 1 NO   |
| Control Circuit Fusing  | 2 fuses primary circuit  |
| Thermal Overload Type   | Melting alloy 3  |
| Disconnect Type         | Non-fusible disconnect switch  |
| Nema Size               | 0  |

### Environment

|                |  |
|----------------|--|
| Enclosure Type | NEMA 1 painted sheet steel with external reset |
|----------------|--|

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications