# **Product data sheet**

Specifications







Transformer, dry type, 75kVA, 3 phase, 208V delta primary, 480Y/277V secondary, 20D, 150C rise

EE75T212H

### Main

Product	Energy Efficient Transformer
Enclosure Code	20D
Enclosure Type	NEMA 2
Insulation Temperature	428 °F (220 °C)
Phase	3 phases
Primary Voltage	208 V delta
Power Rating	75 kVA
Secondary Voltage	480Y/277 V
Full Capacity Taps	3 5 % 1+ 2-
Temperature Rise	150 °C
Winding Material	Aluminium

# **Packing Units**

Apr 25, 2024

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

# **Contractual warranty**

Warranty	18 months
----------	-----------



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>②</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

## **Certifications & Standards**

Eu Rohs Directive	Compliant	
	EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	

### **Dimensions Drawings**

### **Approximate Dimensions**

