



Transformer, Type T, industrial control, 1000VA, 1 phase, 240x480V primary, 24V secondary, 115C rise

9070T1000D2

#### Main

Product Type	Industrial Control Transformer
Туре	Т

# Complementary

Number Of Phases	1 phase	
Power Rating	1000 VA UL	
	1000 VA CSA	
	1000 VA NOM	
	630 VA CE	
Primary To Secondary Voltage	240 x 480 V 24 V	
Temperature Rise	115 °C	
Electrical Connection	Screw clamp terminals	
Height	4.51 in (114.55 mm)	
Width	5.25 in (133.35 mm)	
Depth	6.3 in (160.02 mm)	
Material	Copper: winding	
Fingersafe Cover Compatibility	FSC2	

### **Environment**

Certifications	CSA file LR37055 guide 184-N-90 UL listed file E61239
Enclosure Type	Not rated (open device)
Insulation Temperature	356 °F (180 °C)

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.50 in (21.59 cm)
Package 1 Width	11.00 in (27.94 cm)
Package 1 Length	10.00 in (25.4 cm)
Package 1 Weight	20.20 lb(US) (9.163 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations