

# Product data sheet

Specifications



Mini circuit breaker, E-Frame, 35A, 1 pole, 277 VAC, 65 kA max, bolt on

EGB14035

## Main

Range Of Product	125 A Frame EDB-EGB-EJB
Product Or Component Type	Miniature circuit-breaker
Device Short Name	EGB
Module Type	E-Frame
Trip Unit Rating	1800 A

## Complementary

[In] Rated Current	35 A
Maximum Operating Voltage	277 V AC
Awg Gauge	AWG 12...AWG 2/0 aluminum AWG 14...AWG 2/0 copper
Breaking Capacity	35 kA 277 V AC 35 kA 240 V AC 65 kA 120 V AC 35 kA 120/240 V AC
Circuit Breaker Application	HACR rated HID rated
Electrical Connection	Lugs aluminum
Holding Current	630 A
Local Signalling	Trip indicator
Mounting Mode	Bolt-on
Number Of Poles	1
Number Of Spaces	1
Number Of Spaces Required	1
Product Destination	NF panelboard
Protection Type	Overload Short-circuit
Trip Unit Technology	Thermal-magnetic
Breaking Capacity Code	G
Tightening Torque	34.52 lbf.in (3.9 N.m) 0.00...0.01 in² (2.5...6 mm²) AWG 14...AWG 10) 49.56 lbf.in (5.6 N.m) 0.02...0.11 in² (10...70 mm²) AWG 8...AWG 2/0)
Height	5.66 in (143.76 mm)
Width	0.98 in (24.89 mm)
Depth	4.05 in (102.87 mm)
Net Weight	2 lb(US) (0.91 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Environment

Product Certifications	cULus
Ambient Air Temperature For Operation	104 °F (40 °C)

# Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.80 in (4.572 cm)
Package 1 Width	6.10 in (15.494 cm)
Package 1 Length	10.20 in (25.908 cm)
Package 1 Weight	20.46 oz (579.963 g)

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information