

# Product data sheet

Specifications



Surge protection device,  
Surgelogic, HL, 120kA, 120/240  
VAC, 1 phase, 3 wire, SPD type 1

HL1IMA12C1

## Main

Product	Surge protection device
Range	Surgelogic
Device Short Name	IMA
Type	HL

## Complementary

Voltage Rating	120/240 V AC
Mcov	150 V
Sccr	200 kA
Surge Current	120 kA
Rated Current	60 A
Breaking Capacity	50 kA
Number Of Phases	1 phase
Max Number Of Poles	3
Wiring Configuration	3-wire
Connection	I-Line line Lugs ground AWG 6 copper 35.40 lbf.in (4 N.m) Lugs neutral AWG 6 copper 35.40 lbf.in (4 N.m)
Trip Unit Technology	Thermal-magnetic
Local Signalling	Status LED green per phase normal operation Status LED red per phase fault
Provided Equipment	Alarm enable/disable switch Surge counter Circuit-breaker
Cable Length	19.02 in (483 mm)
Mounting Support	Panel mounting
Height	12.16 in (308.9 mm)
Width	13.46 in (341.9 mm)
Depth	5.59 in (142.1 mm)

## Environment

Enclosure Rating	NEMA 1
------------------	--------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 1449:ed. 3
	CSA C22.2 No 8:1986
	UL 96A:ed. 12
	UL 489:ed. 11
	CSA C22.2 No 5-09

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.00 in (22.86 cm)
Package 1 Width	16.00 in (40.64 cm)
Package 1 Length	17.50 in (44.45 cm)
Package 1 Weight	22.14 lb(US) (10.043 kg)

# Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
Eu Rohs Directive	Compliant	<a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>	Product out of China RoHS scope. Substance declaration for your information