

Circuit breaker, PowerPacT H, 150A, 3 pole, 600VAC, 18kA, lugs, thermal magnetic, 80%

HGL36150

### Main

| Range                     | PowerPact       |
|---------------------------|-----------------|
| Product Name              | PowerPact H     |
| Product Or Component Type | Circuit breaker |
| Device Application        | Distribution    |

### Complementary

| Complementary                            |   |
|--|---|
| [In] Rated Current                       | 150 A   |
| Number Of Poles                          | 3P  |
| Protected Poles Description              | 3t  |
| Control Type                             | Toggle  |
| Breaking Capacity Code                   | G   |
| Breaking Capacity                        | 65 kA 240 V AC 50/60 Hz UL 489<br>35 kA 480 V AC 50/60 Hz UL 489<br>18 kA 600 V AC 50/60 Hz UL 489<br>20 kA 250 V DC UL 489<br>20 kA 500 V DC UL 489  |
| [Ue] Rated Operational Voltage           | 690 V AC 50/60 Hz IEC 60947-3   |
| Network Frequency                        | 50/60 Hz  |
| [Ics] Rated Service Breaking<br>Capacity | 65 kA 220/240 V AC 50/60 Hz IEC 60947-2<br>35 kA 380/440/415 V AC 50/60 Hz IEC 60947-2<br>18 kA 500/525 V AC 50/60 Hz IEC 60947-2<br>20 kA 250 V DC IEC 60947-2<br>20 kA 500 V DC IEC 60947-2 |
| [Uimp] Rated Impulse Withstand Voltage   | 8 kV IEC 60947-2  |
| Trip Unit Technology                     | Thermal-magnetic  |
| Magnetic Tripping Current                | 1700 A  |
| Magnetic Hold Current                    | 900 A   |
| Continuous Current Rating                | 80 %  |
| [Ui] Rated Insulation Voltage            | 750 V IEC 60947-2   |
| Suitability For Isolation                | Yes IEC 60947-2   |
| Utilisation Category                     | Category A  |
| Awg Gauge                                | AWG 14AWG 3/0 aluminum/copper terminal  |
| Local Signalling                         | Switched off (OFF) 1 trip indicator green)  |
| Mounting Mode                            | Unit mount lug)   |
| Mounting Support                         | Lug   |

| <b>Electrical Connection</b> | Lugs, line<br>Lugs, load   |
|------------------------------|--|
| Terminal Identifier          | AL150HD  |
| Tightening Torque            | 44.25 lbf.in (5 N.m) 0.000.01 in² (2.56 mm²) AWG 14AWG 10) 123.91 lbf.in (14 N.m) 0.020.15 in² (1095 mm²) AWG 8AWG 3/0)              |
| Number Of Slots              | 2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in) |
| Power Wire Stripping Length  | 0.63 in (16 mm)  |
| Color                        | Black  |
| Height                       | 6.42 in (163 mm)   |
| Width                        | 4.09 in (104 mm)   |
| Depth                        | 3.39 in (86 mm)  |
| Net Weight                   | 4.85 lb(US) (2.2 kg)   |
| Quantity Per Set             | 1  |
| Communication Interface      | Modbus<br>Ethernet   |
| Circuit Breaker Application  | HACR rated   |

### **Environment**

| Quality Labels                        | CE  |
|---------------------------------------|---|
| Standards                             | UL<br>CSA<br>NEMA<br>NOM-003-SCFI-2000<br>IEC 60947-2 |
| Product Certifications                | UL<br>CSA<br>NOM                                      |
| Ip Degree Of Protection               | Front cover IP40 IEC 60529                            |
| Pollution Degree                      | 3 IEC 60947-1   |
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C)                                  |
| Ambient Air Temperature For Storage   | -58��185 °F (-5085 °C)                                |
| Operating Altitude                    | < 2000 m without derating<br>5000 m with derating     |

# **Packing Units**

| Unit Type Of Package 1       | PCE                   |
|------------------------------|-----------------------|
| Number Of Units In Package 1 | 1                     |
| Package 1 Height             | 7.40 in (18.796 cm)   |
| Package 1 Width              | 5.70 in (14.478 cm)   |
| Package 1 Length             | 8.70 in (22.098 cm)   |
| Package 1 Weight             | 4.10 lb(US) (1.86 kg) |
| Unit Type Of Package 2       | PAL                   |
| Number Of Units In Package 2 | 100                   |
| Package 2 Height             | 36.00 in (91.44 cm)   |

| Package 2 Width  | 40.00 in (101.6 cm)        |
|------------------|----------------------------|
| Package 2 Length | 48.00 in (121.92 cm)       |
| Package 2 Weight | 545.00 lb(US) (247.208 kg) |

## **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

| <b>⊘</b> | Mercury Free               |     |
|----------|----------------------------|-----|
| <b>②</b> | Rohs Exemption Information | Yes |
| <b>②</b> | Pvc Free                   |     |

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Compliant with Exemptions   |
| China Rohs Regulation    | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | End of Life Information   |