Product data sheet

Specification





Contactor, TeSys Deca, 3P(3NO), AC-3/AC-3e, <=440V, 12A, 24V DC coil, screw clamp terminals

LC1D12BD

Main

Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-1 AC-4 AC-3 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC
[le] Rated Operational Current	25 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit 12 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit 12 A (at <140 °F (60 °C)) at <= 440 V AC AC-3e for power circuit
[Uc] Control Circuit Voltage	24 V DC

Complementary

•	
Motor Power Kw	3 kW at 220230 V AC 50/60 Hz (AC-3) 5.5 kW at 380400 V AC 50/60 Hz (AC-3) 5.5 kW at 415440 V AC 50/60 Hz (AC-3) 7.5 kW at 500 V AC 50/60 Hz (AC-3) 7.5 kW at 660690 V AC 50/60 Hz (AC-3) 3.7 kW at 400 V AC 50/60 Hz (AC-4) 3 kW at 220230 V AC 50/60 Hz (AC-3e)
	5.5 kW at 380400 V AC 50/60 Hz (AC-3e)
	5.5 kW at 415440 V AC 50/60 Hz (AC-3e) 7.5 kW at 500 V AC 50/60 Hz (AC-3e)
	7.5 kW at 660690 V AC 50/60 Hz (AC-3e)
Motor Power Hp	0.5 hp at 115 V AC 50/60 Hz for 1 phase motors 2 hp at 230/240 V AC 50/60 Hz for 1 phase motors 3 hp at 200/208 V AC 50/60 Hz for 3 phases motors 3 hp at 230/240 V AC 50/60 Hz for 3 phases motors 7.5 hp at 460/480 V AC 50/60 Hz for 3 phases motors 10 hp at 575/600 V AC 50/60 Hz for 3 phases motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With
[Ith] Conventional Free Air Thermal Current	25 A (at 140 °F (60 °C)) for power circuit 10 A (at 140 °F (60 °C)) for signalling circuit
Irms Rated Making Capacity	250 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1
Rated Breaking Capacity	250 A at 440 V for power circuit conforming to IEC 60947

[Icw] Rated Short-Time Withstand	105 A 104 °F (40 °C) - 10 s for power circuit
Current	210 A 104 °F (40 °C) - 1 s for power circuit
	30 A 104 °F (40 °C) - 10 min for power circuit
	61 A 104 °F (40 °C) - 1 min for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
_	40 A gG at <= 690 V coordination type 1 for power circuit
	25 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2.5 mOhm - Ith 25 A 50 Hz for power circuit
Power Dissipation Per Pole	0.36 W AC-3
. one. Discipation . o o.o	1.56 W AC-1
	0.36 W AC-3e
	0.00 W 710 00
[Ui] Rated Insulation Voltage	Power circuit 690 V IEC 60947-4-1
	Power circuit 600 V CSA
	Power circuit 600 V UL
	Signalling circuit 690 V IEC 60947-1
	Signalling circuit 600 V CSA
	Signalling circuit 600 V UL
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1
•	B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	30 Mcycles
	30 INICYCLES
Electrical Durability	2 Mcycles 12 A AC-3 <= 440 V
	0.8 Mcycles 25 A AC-1 <= 440 V
	2 Mcycles 12 A AC-3e <= 440 V
Control Circuit Type	DC standard
Coil Technology	With integral suppression device
Control Circuit Voltage Limits	0.10.25 Uc -40158 °F (-4070 °C) drop-out DC
-	0.71.25 Uc -40140 °F (-4060 °C) operational DC
	11.25 Uc 140158 °F (6070 °C) operational DC
Inrush Power In W	5.4 W 68 °F (20 °C))
Hold-In Power Consumption In W	5.4 W 68 °F (20 °C)
Operating Time	63 ±15 % ms closing
	20 ±20 % ms opening
Time Constant	28 ms
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)
. •	

Connections - Terminals	Power circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: flexible without cable end		
	Power circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness:		
	flexible without cable end Power circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness:		
	flexible with cable end Power circuit: screw clamp terminals 2 0.000.00 in² (12.5 mm²) - cable stiffness:		
	flexible with cable end		
	Power circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end		
	Power circuit: screw clamp terminals 2 0.000.01 in ² (14 mm ²) - cable stiffness: solid without cable end		
	Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness:		
	flexible without cable end Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness:		
	flexible without cable end Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness:		
	flexible with cable end Control circuit: screw clamp terminals 2 0.000.00 in² (12.5 mm²) - cable stiffness:		
	flexible with cable end		
	Control circuit: screw clamp terminals 1 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end		
	Control circuit: screw clamp terminals 2 0.000.01 in² (14 mm²) - cable stiffness: solid without cable end		
Fightening Torque	Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm		
	Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2		
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2		
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2		
	Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2		
Auxiliary Contact Composition 1 NO + 1 NC			
Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1		
Signalling Circuit Frequency 25400 Hz			
Minimum Switching Voltage	17 V for signalling circuit		
Minimum Switching Current	5 mA for signalling circuit		
nsulation Resistance	> 10 MOhm for signalling circuit		
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact1.5 ms on energisation between NC and NO contact		
Mounting Support	Plate		
	Rail		
Environment			
Standards	CSA C22.2 No 14		
	EN 60947-4-1		
	EN 60947-5-1 IEC 60947-4-1		
	IEC 60947-5-1		
	UL 508 IEC 60335-1		
Product Certifications	BV		
	CSA		
	DNV		
	RINA GL		
	GOST		
	LROS (Lloyds register of shipping) CCC		
	UL		
p Degree Of Protection	UKCA IP20 front face IEC 60529		
Protective Treatment	THIEC 60068-2-30		
Climatic Withstand	IACS E10 exposure to damp heat		
IEC 60947-1 Annex Q category D exposure to damp heat			

Permissible Ambient Air Temperature Around The Device	-40140 °F (-4060 °C) 140158 °F (6070 °C) with derating	
Operating Altitude	03000 m	
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1	
Flame Retardance	V1 UL 94	
Mechanical Robustness	Vibrations contactor open 2 Gn, 5300 Hz) Vibrations contactor closed 4 Gn, 5300 Hz) Shocks contactor open 10 Gn for 11 ms) Shocks contactor closed 15 Gn for 11 ms)	
Height	3.03 in (77 mm)	
Width	1.77 in (45 mm)	
Depth	3.74 in (95 mm)	
Net Weight	1.07 lb(US) (0.485 kg)	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	3.54 in (9.000 cm)
Package 1 Length	4.33 in (11.000 cm)
Package 1 Weight	18.35 oz (520.300 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	15
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	17.72 lb(US) (8.039 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	240
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	301.20 lb(US) (136.620 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	


Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Compliant with Exemptions		
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information		
Environmental Disclosure	Product Environmental Profile		
Circularity Profile	End of Life Information		

LC1D12BD

Dimensions Drawings

Dimensions



(1) Minimum electrical clearance

LC1		D09D18	D093D123	D099D129
b		77	99	80
	without cover or add-on blocks	93	93	93
С	with cover, without add-on blocks	95	95	95
с1	with LAD N or C (2 or 4 contacts)	126	126	126
c2	with LA6 DK10	138	138	138
c 3	with LAD T, R, S	146	146	146
	with LAD T, R, S and sealing cover	150	150	150

Product data sheet

LC1D12BD

Connections and Schema

Wiring

