Product data sheet

Specifications



Circuit breaker, LA, 300A, 2 pole, 600VAC, 22kA, 250VDC, 10kA, lugs, thermal magnetic

LAL26300

Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic
Complementary	
[In] Rated Current	300 A
Number Of Poles	2P
Mounting Mode	Unit mount
Magnetic Hold Current	1500 A
Magnetic Tripping Current	3000 A
Electrical Connection	Lugs, load Lugs, line
Terminal Identifier	AL400LA
Tightening Torque	115.06 lbf.in (13 N.m) 0.070.47 in² (42304 mm²) AWG 1600 kcmil) 115.06 lbf.in (13 N.m) 0.070.20 in² (42127 mm²) AWG 1250 kcmil)
Height	11 in (279.40 mm)
Width	6 in (152.40 mm)
Depth	5.84 in (148.34 mm)
Circuit Breaker Application	HACR rated

Environment

Certifications	UL listed
	IEC
	CSA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.02 in (22.9 cm)
Package 1 Width	11.50 in (29.2 cm)
Package 1 Length	17.52 in (44.5 cm)
Package 1 Weight	14.42 lb(US) (6.54 kg)

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations