

Product data sheet

Specifications



PowerLogic EM3500 DIN rail meter - Modbus 4 quadrant - current transformer

METSEEM3555

Main

Range	PowerLogic
Range Of Product	PowerLogic EM3500
Device Short Name	EM3555
Product Or Component Type	Energy meter
Metering Type	Peak demand power PM, QM, SM Current I1, I2, I3, Iavg Active, reactive, apparent energy (signed, four quadrant) Demand power P, Q, S Voltage U21, U32, U13, V1, V2, V3

Complementary

Poles Description	3P + N
Type Of Measurement	Active and reactive power total Active and reactive power per phase Apparent power total Apparent power per phase Power factor total Power factor per phase Peak demand power Current Voltage Frequency
Device Application	Partial meter Sub billing
Accuracy Class	Class 0.2S power IEC 62053-22 Class 0.2S energy IEC 62053-22 Class 0.2S power ANSI C12.20 Class 0.2S energy ANSI C12.20
Measurement Accuracy	Power +/- 0.2 % Energy +/- 0.2 %
Input Type	Split core current transducer 0.333 V or 1 V
Rated Voltage	90...347 V
Network Frequency	60 Hz 50 Hz
Technology Type	Electronic
Display Type	Backlit LCD
Measurement Current	5...32000 A
Display Digits	5

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Information Displayed	Status and alert Communication with system Input/output status Error Tx activity Rx activity Instant power per usage
Tamperproof Of Settings	Protected by access code
Communication Port Protocol	Modbus RTU 1200...38400 bps - 2-wire
Communication Port Support	Screw terminal block RS485
Communication Of Data	Instantaneous and demand values Lifetime energy production
Communication Service	Total cumulated active energy Total cumulated energy
Data Recording	Energy consumption logs Time stamping
Demand Intervals	External synchronisation to communication Fixed or rolling block
Local Signalling	Red LED threshold reached Green flashing LED output signal
Number Of Outputs	1 alarm output 1 pulse
Buffer Size	16-bit 10
[Ue] Rated Operational Voltage	90...347 V AC 50/60 Hz between phase and neutral UL 156...600 V AC 50/60 Hz between phases UL 90...300 V AC 50/60 Hz between phase and neutral CE 125...300 V DC
Power Consumption In Va	5 VA 347 V AC between phase and neutral) 5 VA 600 V AC between phases)
Power Consumption In W	3 W 300 V
Ride-Through Time	100 ms 120 V AC
Mounting Mode	Clip-on By screws
Mounting Support	DIN rail
Standards	CSA C22.2 No 14-05 UL 508 IEC 61010-1
Product Certifications	CE IEC 61010 CULus UL 508

Environment

Relative Humidity	0...95 %
Ambient Air Temperature For Operation	-22...158 °F (-30...70 °C)
Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C)
Colour	Dark grey
9 Mm Pitches	12
Width	4.21 in (107 mm)
Height	3.58 in (91 mm)
Depth	2.32 in (59 mm)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.58 in (9.1 cm)
Package 1 Width	4.21 in (10.7 cm)
Package 1 Length	2.32 in (5.9 cm)
Package 1 Weight	8.00 lb(US) (3.629 kg)

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins