Product data sheet

Specifications





PowerLogic PM8000 - I/O Module - Analogue - 4 inputs + 2 outputs

METSEPM89M0024

Main

Range	PowerLogic
Product Or Component Type	I/O module
Device Application	Optional expansion module
Range Compatibility	PowerLogic PowerLogic PM8000 PowerLogic PowerLogic ION7400 PowerLogic PowerLogic ION9000

Complementary

	5
Number Of Outputs	2 analog, 0-20 mA or 4-20 mA 010 V
Number Of Inputs	4 analog 020 mA/420 mA 030 V
Width	0.87 in (22 mm)
Depth	3.56 in (90.5 mm)
Height	3.56 in (90.5 mm)
Net Weight	4.94 oz (140 g)

Environment

Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Ip Degree Of Protection	IP30 conforming to IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.36 in (6 cm)
Package 1 Width	3.94 in (10 cm)
Package 1 Length	4.72 in (12 cm)
Package 1 Weight	7.87 oz (223 g)

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information