



Automatic switch, PowerPacT Q, 225A, 2 pole, 480VAC, lugs, magnetic

QBL22000S22

Main

Product Or Component Type	Automatic switch
Range Of Product	PowerPact Q
Trip Unit Technology	Magnetic
Circuit Breaker Type	Q-Frame

Complementary

[In] Rated Current	225 A
[Ue] Rated Operational Voltage	240 V AC
Mounting Mode	Unit mount
Poles Description	2P
Short-Circuit Withstand	10 kA 240 V UL 489
Breaking Capacity Code	В
Electrical Connection	Lugs, line Lugs, load
Awg Gauge	x AWG 4300 kcmil (aluminum/copper)
Magnetic Tripping Current	4500 A
Height	16.24 in (412.50 mm)
Width	16.54 in (420.12 mm)
Depth	14.49 in (368.05 mm)
Tightening Torque	247.82 lbf.in (28 N.m) 0.040.23 in² (25150 mm²) AWG 4300 kcmil)

Environment

Product Certifications	IEC UL listed
	CSA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.56 in (14.127 cm)
Package 1 Width	5.81 in (14.757 cm)
Package 1 Length	9.75 in (24.765 cm)
Package 1 Weight	3.36 lb(US) (1.525 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Pvc Free	
⊘	Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations