Product data sheet

Specification





Pendant control station, Harmony XAC, plastic, yellow, pistol grip, 2 push buttons with 1NO, 1 emergency stop NC

XACA2013

Main

Range Of Product	Harmony XAC
Product Or Component Type	Pendant control station
Device Short Name	XACA pistol grip

Complementary

Complementary		
Control Station Type	Double insulated	
Enclosure Material	Polypropylene	
Control Type	Intuitive	
Electrical Circuit Type	Control circuit	
Enclosure Type	Complete ready for use	
Control Station Application	Control of single speed hoist motor	
Control Station Composition	2 push-buttons + 1 emergency stop	
Control Button Type	First push-button 1 NO raise, slow Second push-button 1 NO lower, slow Stop push-button Ø 30 mm 1 NC latching	
Product Compatibility	ZB2BE101 for each direction ZB2BE102 for emergency stop	
Mechanical Interlocking	With mechanical interlocking	
Control Station Colour	Yellow	
Connections - Terminals	Screw clamp terminals, 1 x 2.5 mm^2 with or without cable end Screw clamp terminals, $2 \times 1.5 \text{ mm}^2$ with or without cable end	
Standards	CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60204-32 UL 508	
Product Certifications	CSA UL	
Protective Treatment	TH	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Vibration Resistance	15 gn 10500 Hz)IEC 60068-2-6	
Shock Resistance	100 gn IEC 60068-2-27	
Overvoltage Category	Class II IEC 61140	
Ip Degree Of Protection	IP65 IEC 60529	
Ik Degree Of Protection IK08 conforming to EN 50102		

Mechanical Durability	1000000 cycles	
Cable Entry	Rubber sleeve with stepped entry 0.280.59 in (715 mm)	
Contact Code Designation	A600 AC-15, Ue = 240 V, Ie = 3 A IEC 60947-5-1 appendix A A600 AC-15, Ue = 600 V, Ie = 1.2 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 250 V, Ie = 0.27 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 600 V, Ie = 0.1 A IEC 60947-5-1 appendix A	
[Ithe] Conventional Enclosed Thermal Current	10 A	
[Ui] Rated Insulation Voltage	600 V 3)IEC 60947-1	
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-1	
Contact Operation	Slow-break	
Maximum Resistance Across Terminals	oss 25 MOhm	
Operating Force	1315 N	
Short-Circuit Protection	10 A fuse protection cartridge gG	
Rated Operational Power In W	40 W DC-13 1000000 cycles 60 cyc/mn 120 V 0.5 inductive IEC 60947-5-1 appendix C 48 W DC-13 1000000 cycles 60 cyc/mn 48 V 0.5 inductive IEC 60947-5-1 appendix C 65 W DC-13 1000000 cycles 60 cyc/mn 24 V 0.5 inductive IEC 60947-5-1 appendix C	
Terminals Description Iso N°1	(13-14)NO	
Terminals Description Iso N°2	(11-12)NC	
erminal Identifier (11-12)NC (13-14)NO		
Net Weight	0.68 lb(US) (0.31 kg)	

Packing Units

_		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	2.17 in (5.500 cm)	
Package 1 Width	3.54 in (9.000 cm)	
Package 1 Length	11.81 in (30.000 cm)	
Package 1 Weight	11.71 oz (332.000 g)	
Unit Type Of Package 2	S03	
Number Of Units In Package 2	15	
Package 2 Height	11.81 in (30.000 cm)	
Package 2 Width	11.81 in (30.000 cm)	
Package 2 Length	15.75 in (40.000 cm)	
Package 2 Weight	12.08 lb(US) (5.480 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations