



Circuit breaker, PowerPacT Q, 150A, 3 pole, 240VAC, 25kA, busbar, thermal magnetic, 80%

QDF32150TS

Main

Range	PowerPact
Product Name	PowerPact Q
Product Or Component Type	Circuit breaker
Device Application	Distribution

Complementary

150 A
3P
Operating handle
D
25 kA 120/208 V AC 50/60 Hz UL 25 kA 240 V AC 50/60 Hz UL
240 V AC 50/60 Hz UL
50/60 Hz
8 kV UL
Thermal-magnetic
2400 A
1200 A
80 %
Category A
1000 cycles loaded 5000 cycles no load
1 trip indicator green)
Unit mount busbar)
Busbar
Busbar connection, line Busbar connection, load
247.82 lbf.in (28 N.m) 0.040.23 in² (25150 mm²) AWG 4300 kcmil)
0.87 in (22 mm)
6.47 in (164.34 mm)
4.5 in (114.30 mm)
3.93 in (99.82 mm)

Circuit Breaker Application	HACR rated
Environment	
Standards	UL CSA NEMA NOM-003-SCFI-2000
Product Certifications	UL CSA NOM
Ambient Air Temperature For Operation	104158 °F (4070 °C)
Packing Units	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.56 in (14.127 cm)
Package 1 Width	5.81 in (14.757 cm)

9.75 in (24.765 cm)

4.55 lb(US) (2.065 kg)

Package 1 Length

Package 1 Weight



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Mercury Free	
Ø	Rohs Exemption Information	Yes
⊘	Pvc Free	
⊘	Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations