



Generator panel, QO, 1 phase, 40 spaces, 80 circuits, 150A main breaker, PoN, NEMA1, cover with door, CSA

QOGP3P604436150P

Main

Marketing Trade Name	QO
Product Type	Panel

Complementary

Tightening Torque	Cover 20 lb.in
Load Center Type	PoN Convertible Mains (breaker)
Rated Current	150 A
	60 A
Number Of Spaces	40
Max Short Circuit Current Rating	10 kA
Maximum Number Of Single Pole Circuits	80
Number Of Phases	1 phase
Ground Bar	Grounding bar (ordered separately)
Height	39.37 in (1000 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	CSA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	39.37 in (100.0 cm)
Package 1 Width	14.25 in (36.2 cm)
Package 1 Length	3.74 in (9.5 cm)
Package 1 Weight	40.00 lb(US) (18.144 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations