# Product data sheet

Specifications





# compact smart relay, Zelio Logic SR2 SR3, 12 IO, 12V DC, clock, display

SR2B121JD

### Main

Range Of Product	Zelio Logic
Product Or Component Type	Compact smart relay

## Complementary

Complementary	
Local Display	With
Number Or Control Scheme Lines	0240 ladder 0500 FBD
Cycle Time	690 ms
Backup Time	10 years 77 °F (25 °C)
Clock Drift	12 min/year 32131 °F (055 °C) 6 s/month 77 °F (25 °C)
Checks	Program memory on each power up
[Us] Rated Supply Voltage	12 V DC
Supply Voltage Limits	10.414.4 V
Maximum Supply Current	120 mA without extension)
Power Dissipation In W	1.5 W without extension
Reverse Polarity Protection	With
Discrete Input Number	8 IEC 61131-2 Type 1
Discrete Input Type	Resistive
Discrete Input Voltage	12 V DC
Discrete Input Current	4 mA
Counting Frequency	1 kHz discrete input
Voltage State 1 Guaranteed	>= 7 V IBIG used as discrete input circuit >= 5.6 V I1IA and IHIR discrete input circuit
Voltage State 0 Guaranteed	<= 3 V IBIG used as discrete input circuit <= 2.4 V I1IA and IHIR discrete input circuit
Current State 1 Guaranteed	>= 2 mA I1IA and IHIR discrete input circuit) >= 0.5 mA IBIG used as discrete input circuit)
Current State 0 Guaranteed	<= 0.2 mA IBIG used as discrete input circuit) <= 0.9 mA I1IA and IHIR discrete input circuit)
Input Compatibility	3-wire proximity sensors PNP discrete input
Analogue Input Number	4
Analogue Input Type	Common mode
Analogue Input Range	010 V 012 V

Maximum Permissible Voltage	14.4 V analogue input circuit
Analogue Input Resolution	8 bits at maximum voltage
Lsb Value	39 mV analogue input circuit
Conversion Time	Smart relay cycle time analogue input circuit
Conversion Error	+/- 5 % 77 °F (25 °C) analogue input circuit +/- 6.2 % 131 °F (55 °C) analogue input circuit
Repeat Accuracy	+/- 2 % 131 °F (55 °C) analogue input circuit
Operating Distance	10 m between stations, with screened cable (sensor not isolated) analogue input circuit
Input Impedance	14 kOhm IBIG used as analogue input circuit 14 kOhm IBIG used as discrete input circuit 2.7 kOhm I1IA and IHIR discrete input circuit
Number Of Outputs	4 relay
Output Voltage Limits	24250 V AC relay output) 530 V DC relay output)
Contacts Type And Composition	NO relay output
Output Thermal Current	8 A for all 4 outputs relay output
Electrical Durability	AC-12 500000 cycles 230 V, 1.5 A relay output IEC 60947-5-1 AC-15 500000 cycles 230 V, 0.9 A relay output IEC 60947-5-1 DC-12 500000 cycles 24 V, 1.5 A relay output IEC 60947-5-1 DC-13 500000 cycles 24 V, 0.6 A relay output IEC 60947-5-1
Switching Capacity In Ma	>= 10 mA 12 V relay output)
Operating Rate In Hz	0.1 Hz at le)relay output 10 Hz no load)relay output
Mechanical Durability	10000000 cycles relay output
[Uimp] Rated Impulse Withstand Voltage	4 kV EN/IEC 60947-1 and EN/IEC 60664-1
Clock	With
Response Time	10 ms from state 0 to state 1)relay output 5 ms from state 1 to state 0)relay output
Connections - Terminals	Screw terminals, 1 x 0.21 x 2.5 mm <sup>2</sup> AWG 25AWG 14) semi-solid Screw terminals, 1 x 0.21 x 2.5 mm <sup>2</sup> AWG 25AWG 14) solid Screw terminals, 1 x 0.251 x 2.5 mm <sup>2</sup> AWG 24AWG 14) flexible with cable end Screw terminals, 2 x 0.22 x 1.5 mm <sup>2</sup> AWG 24AWG 16) solid Screw terminals, 2 x 0.252 x 0.75 mm <sup>2</sup> AWG 24AWG 18) flexible with cable end
Tightening Torque	4.43 lbf.in (0.5 N.m)
Overvoltage Category	III IEC 60664-1

# Environment

Immunity To Microbreaks	1 ms repeated 20 times
Product Certifications	C-Tick UL CSA GOST GL

Standards	IEC 61000-4-11 IEC 60068-2-6 Fc IEC 61000-4-12 IEC 61000-4-2 level 3 IEC 61000-4-5 IEC 61000-4-3 IEC 61000-4-4 level 3 IEC 60068-2-27 Ea IEC 61000-4-6 level 3
Ip Degree Of Protection	IP20 IEC 60529 terminal block) IP40 IEC 60529 front panel)
Environmental Characteristic	EMC directive IEC 61000-6-2 EMC directive IEC 61000-6-3 EMC directive IEC 61000-6-4 EMC directive IEC 61131-2 zone B Low voltage directive IEC 61131-2
Disturbance Radiated/Conducted	Class B EN 55022-11 group 1
Pollution Degree	2 IEC 61131-2
Ambient Air Temperature For Operation	-4104 °F (-2040 °C) in non-ventilated enclosure IEC 60068-2-1 and IEC 60068-2-2 -4131 °F (-2055 °C) IEC 60068-2-1 and IEC 60068-2-2
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Operating Altitude	2000 m
Maximum Altitude Transport	10000.00 ft (3048 m)
Relative Humidity	95 % without condensation or dripping water

# **Packing Units**

Unit Type Of Package 1PCENumber Of Units In Package 11Package 1 Height2.68 in (6.8 cm)Package 1 Width3.54 in (9.0 cm)Package 1 Length3.94 in (10.0 cm)Package 1 Weight8.43 oz (239.0 g)Unit Type Of Package 2S03Number Of Units In Package 230Package 2 Height11.81 in (30.0 cm)Package 2 Width11.81 in (30.0 cm)Package 2 Length15.75 in (40.0 cm)		
Package 1 Height2.68 in (6.8 cm)Package 1 Width3.54 in (9.0 cm)Package 1 Length3.94 in (10.0 cm)Package 1 Weight8.43 oz (239.0 g)Unit Type Of Package 2S03Number Of Units In Package 230Package 2 Height11.81 in (30.0 cm)Package 2 Width11.81 in (30.0 cm)	Unit Type Of Package 1	PCE
Package 1 Width3.54 in (9.0 cm)Package 1 Length3.94 in (10.0 cm)Package 1 Weight8.43 oz (239.0 g)Unit Type Of Package 2S03Number Of Units In Package 230Package 2 Height11.81 in (30.0 cm)Package 2 Width11.81 in (30.0 cm)	Number Of Units In Package 1	1
Package 1 Length3.94 in (10.0 cm)Package 1 Weight8.43 oz (239.0 g)Unit Type Of Package 2S03Number Of Units In Package 230Package 2 Height11.81 in (30.0 cm)Package 2 Width11.81 in (30.0 cm)	Package 1 Height	2.68 in (6.8 cm)
Package 1 Weight8.43 oz (239.0 g)Unit Type Of Package 2S03Number Of Units In Package 230Package 2 Height11.81 in (30.0 cm)Package 2 Width11.81 in (30.0 cm)	Package 1 Width	3.54 in (9.0 cm)
Unit Type Of Package 2 S03   Number Of Units In Package 2 30   Package 2 Height 11.81 in (30.0 cm)   Package 2 Width 11.81 in (30.0 cm)	Package 1 Length	3.94 in (10.0 cm)
Number Of Units In Package 2 30   Package 2 Height 11.81 in (30.0 cm)   Package 2 Width 11.81 in (30.0 cm)	Package 1 Weight	8.43 oz (239.0 g)
Package 2 Height     11.81 in (30.0 cm)       Package 2 Width     11.81 in (30.0 cm)	Unit Type Of Package 2	S03
Package 2 Width     11.81 in (30.0 cm)	Number Of Units In Package 2	30
	Package 2 Height	11.81 in (30.0 cm)
Package 2 Length     15.75 in (40.0 cm)	Package 2 Width	11.81 in (30.0 cm)
	Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight     17.14 lb(US) (7.775 kg)	Package 2 Weight	17.14 lb(US) (7.775 kg)

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance




### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

**Dimensions Drawings** 


#### Compact and Modular Smart Relays

#### Mounting on 35 mm/1.38 in. DIN Rail




#### (1) With SR2USB01 or SR2BTC01

#### Screw Fixing (Retractable Lugs)



(1) With SR2USB01 or SR2BTC01


#### **Position of Display**



Connections and Schema


#### Compact and Modular Smart Relays

#### Connection of Smart Relays on DC Supply



- (1) 1 A quick-blow fuse or circuit-breaker.
- (2) Fuse or circuit-breaker.
- (3) Inductive load.
- (4) Q9 and QA: 5 A (max. current in terminal C: 10 A).

#### **Discrete Input Used for 3-Wire Sensors**




(1) 1 A quick-blow fuse or circuit-breaker.

#### Performance Curves

#### Compact and Modular Smart Relays

#### **Electrical Durability of Relay Outputs**

(in millions of operating cycles, conforming to IEC/EN 60947-5-1) DC-12 (1)




#### X: Current (A)

Y: Millions of operating cycles

(1) DC-12: control of resistive loads and of solid state loads isolated by opto-coupler,  $L/R \le 1$  ms.

DC-13 (1)



#### X: Current (A)

Y: Millions of operating cycles

(1) DC-13: switching electromagnets,  $L/R \le 2 \times (Ue \times Ie)$  in ms, Ue: rated operational voltage, Ie: rated operational current (with a protection diode on the load, DC-12 curves must be used with a coefficient of 0.9 applied to the number in millions of operating cycles).