Product data sheet





safety module, Harmony XPS, estop or guard, connected to supply terminals 48 to 240V AC or DC, no inputs, screw

XPSBAC34AP

Main

viaiii				
Range Of Product	Harmony Safety Automation			
Product Or Component Type	Safety module			
Safety Module Name	XPSBAC			
Safety Module Application	For emergency stop and protective guard applications			
Function Of Module	Emergency stop button with 2 NC contacts Guard monitoring with 1 or 2 limit switches			
Safety Level	Can reach PL e/category 4 for normally open relay contact ISO 13849-1 Can reach SILCL 3 for normally open relay contact IEC 62061 Can reach SIL 3 for normally open relay contact IEC 61508 Can reach PL c/category 1 for normally closed relay contact ISO 13849-1 Can reach SILCL 1 for normally closed relay contact IEC 62061 Can reach SIL 1 for normally closed relay contact IEC 61508			
Safety Reliability Data	Can reach SIL 1 for normally closed relay contact IEC 61508 MTTFd > 30 years for normally open relay contact ISO 13849-1 Dcavg >= 99 % for normally open relay contact ISO 13849-1 PFHd = 1.01E-09 for normally open relay contact ISO 13849-1 HFT = 1 for normally open relay contact IEC 62061 PFHd = 1.01E-09 for normally open relay contact IEC 62061 SFF > 99% for normally open relay contact IEC 62061 HFT = 1 for normally open relay contact IEC 61508-1 PFHd = 1.01E-09 for normally open relay contact IEC 61508-1 SFF > 99% for normally open relay contact IEC 61508-1 Type = B for normally open relay contact IEC 61508-1 MTTFd > 30 years for normally closed relay contact ISO 13849-1 DC > 60 % for normally closed relay contact ISO 13849-1 PFHd = 1.01E-09 for normally closed relay contact ISO 13849-1 HFT=0 for normally closed relay contact IEC 62061 PFHd = 1.01E-09 for normally closed relay contact IEC 62061 SFF > 60% for normally closed relay contact IEC 62061 HFT=0 for normally closed relay contact IEC 62061 FFHd = 1.01E-09 for normally closed relay contact IEC 62061 SFF > 60% for normally closed relay contact IEC 61508-1 SFF > 60% for normally closed relay contact IEC 61508-1 SFF > 60% for normally closed relay contact IEC 61508-1 SFF > 60% for normally closed relay contact IEC 61508-1			
Electrical Circuit Type	NC pair			
Connections - Terminals	Removable screw terminal block, 0.22.5 mm² solid or flexible Removable screw terminal block, 0.252.5 mm² flexible with ferrule single conductor Removable screw terminal block, 0.21.5 mm² solid or flexible twin conductor Removable screw terminal block, 2 x 0.251 mm² flexible with ferrule without cable end, with bezel Removable screw terminal block, 2 x 0.51.5 mm² flexible with ferrule with cable end, with bezel			
[Us] Rated Supply Voltage	age 48240 V AC - 1510 % 48240 V DC - 2020 %			

Complementary

Synchronisation Time Between Inputs	Unlimited
Type Of Start	Automatic/manual/monitored
Power Consumption In W	2.0 W 48240 V DC

Life Is On Schneider Apr 23, 2024

Power Consumption In Va	nption In Va 6.0 VA 48240 V AC 50/60 Hz				
Input Protection Type	Internal, electronic				
Safety Outputs	4 NO + 1 NC				
Safety Inputs	0				
Input Compatibility	Normally closed circuit ISO 14119 XC limit switch ISO 14119 Mechanical contact ISO 14119 Normally closed circuit ISO 13850				
Input Terminal	Power supply				
[le] Rated Operational Current	5 A AC-1 for normally open relay contact 3 A AC-15 for normally open relay contact 5 A DC-1 for normally open relay contact 3 A DC-13 for normally open relay contact 3 A AC-1 for normally closed relay contact 1 A AC-15 for normally closed relay contact 3 A DC-1 for normally closed relay contact 1 A DC-13 for normally closed relay contact				
Control Outputs	0				
[Ith] Conventional Free Air Thermal Current	6 A				
Associated Fuse Rating	10 A gG NO relay output circuit IEC 60947-1				
Minimum Output Current	10 mA relay output				
Minimum Output Voltage	5 V relay output				
Response Time	60 ms at 48240 V AC/DC				
[Ui] Rated Insulation Voltage	300 V 2)IEC 60947-1				
[Uimp] Rated Impulse Withstand Voltage	4 kV II IEC 60947-1				
Local Signalling	LED green power power ON LED red error error LED yellow state status LED yellow start1 start input LED yellow start2 start input				
Mounting Support	35 mm symmetrical DIN rail				
Depth	4.72 in (120 mm)				
Height	3.94 in (100 mm)				
Width	0.89 in (22.5 mm)				
Net Weight	0.44 lb(US) (0.200 kg)				

Environment

Ambient Air Temperature For Operation	-13131 °F (-2555 °C)		
Standards	IEC 60947-5-1		
	IEC 61508-1 functional safety standard		
	IEC 61508-2 functional safety standard		
	IEC 61508-3 functional safety standard		
	IEC 61508-4 functional safety standard		
	IEC 61508-5 functional safety standard		
	IEC 61508-6 functional safety standard		
	IEC 61508-7 functional safety standard		
	ISO 13849-1 functional safety standard		
	IEC 62061 functional safety standard		
Product Certifications	TÜV		
	cULus		
Ip Degree Of Protection	IP20 terminals)IEC 60529 IP40 housing)IEC 60529		
	IP54 mounting area)IEC 60529		

Relative Humidity 5...95 % non-condensing

Packing Units

Unit Type Of Package 1	PCE			
Number Of Units In Package 1	1			
Package 1 Height	2.56 in (6.500 cm)			
Package 1 Width	5.31 in (13.500 cm)			
Package 1 Length	6.10 in (15.500 cm)			
Package 1 Weight	11.11 oz (315.000 g)			
Unit Type Of Package 2	S03			
Number Of Units In Package 2	16			
Package 2 Height	11.81 in (30.000 cm)			
Package 2 Width	11.81 in (30.000 cm)			
Package 2 Length	15.75 in (40.000 cm)			
Package 2 Weight	12.74 lb(US) (5.780 kg)			

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes


Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	End of Life Information		

Dimensions Drawings

Dimensions

Front and Side Views




- (A): Product drawing
 (B): Screw clamp terminal
- (C) : Side view
- (1): Removable terminal blocks, top
- (2): Removable terminal blocks, bottom
- (3): LED indicators
- (4) : Sealable transparent cover


mm in.	7.0–8.0 0.28–0.31					
	mm²	0,2 2,5	0,252,5	0,21,5	0,251	1 0,51,5
	AWG	24 12	2412	2416	2418	3 2016
		()c@m		Nm	0.5 0.6	
Ø 3,5 mm (0.14 in)		(.06	سرره	lb-in	4,4 5,3	

Mounting and Clearance

Mounting to DIN rail




Screw-mounting



Connections and Schema

Wiring Diagram



- (1): A1-A2 (Power supply)
 (2): Y1 (Control output of Start/Restart input), Y2 (Input channel for automatic/manual start/restart), Y3 (Input channel for monitored start/restart with falling edge)
- 13-14-23-24-33-34-43-44-51/61-52-62 : Terminals of the safety-related outputs