Product data sheet

Specifications





Preventa safety module XPSAF, emergency stop, 24VAC DC

XPSAFL5130

- Discontinued on: Jun 30, 2021
- ! End-of-service on: Dec 31, 2023

! Discontinued

Main

Mani	
Range Of Product	Preventa Safety automation
Product Or Component Type	Preventa safety module
Safety Module Name	XPSAF
Safety Module Application	For emergency stop, switch and safety light curtain monitoring
Function Of Module	Monitoring of electro-sensitive protection equipment (ESPE)
	Monitoring of a movable guard Emergency stop with 2 NC contacts monitoring 2-channel wiring
	Emergency stop with 2 No contacts monitoring 2-channel witing Emergency stop monitoring 1-channel wiring
	Multiple emergency stop monitoring 2-channel wiring
Safety Level	Can reach PL e/category 4 ISO 13849-1
	Can reach SILCL 3 IEC 62061
Safety Reliability Data	DC > 99 % ISO 13849-1
,	MTTFd = 172.1 years ISO 13849-1
	PFHd = 5.61E-9 1/h IEC 62061
Type Of Start	Unmonitored
Connections - Terminals	Captive screw clamp terminals, 1 x 0.141 x 2.5 mm² flexible with cable end, with
	double bezel
	Captive screw clamp terminals, 1 x 0.141 x 2.5 mm ² solid with cable end, with double bezel
	Captive screw clamp terminals, 1 x 0.251 x 1.5 mm² flexible with cable end, with
	double bezel
	Captive screw clamp terminals, 1 x 0.251 x 2.5 mm² flexible with cable end, with
	double bezel
	Captive screw clamp terminals, 2 x 0.142 x 0.75 mm ² flexible with cable end, with double bezel
	Captive screw clamp terminals, 2 x 0.142 x 0.75 mm² solid with cable end, with
	double bezel
	Captive screw clamp terminals, 2 x 0.252 x 1 mm ² flexible with cable end, with
	double bezel
	Captive screw clamp terminals, 2 x 0.52 x 1.5 mm² flexible with cable end, with
	double bezel
Output Type	Relay instantaneous opening, 3 NO, volt-free
Number Of Additional Circuits	0
[Us] Rated Supply Voltage	24 V AC - 1510 %
	24 V DC - 1510 %

Complementary

Synchronisation Time Between Inputs	Unlimited
Supply Frequency	50/60 Hz
Maximum Power Consumption In Va	5 VA AC
Input Protection Type	Internal, electronic

Apr 25, 2024 Life Is On Schneider

[Uc] Control Circuit Voltage	241/
	24 V
Maximum Line Resistance	90 Ohm
Breaking Capacity	180 VA holding AC-15 C300 relay output
	1800 VA inrush AC-15 C300 relay output
Breaking Capacity	1.5 A 24 V DC-13)50 ms relay output
Output Thermal Current	6 A per relay relay output
[Ith] Conventional Free Air Thermal Current	18 A
Associated Fuse Rating	4 A gG or gL relay output EN/IEC 60947-5-1, DIN VDE 0660 part 200 6 A fast blow relay output EN/IEC 60947-5-1, DIN VDE 0660 part 200
Minimum Output Current	10 mA relay output
Minimum Output Voltage	17 V relay output
Maximum Response Time On Input Open	40 ms
[Ui] Rated Insulation Voltage	300 V 2)IEC 60947-5-1
	300 V 2)DIN VDE 0110 part 1
[Uimp] Rated Impulse Withstand	4 kV III IEC 60947-5-1
Voltage	4 kV III DIN VDE 0110 part 1
Local Signalling	3 LEDs
Current Consumption	30 mA 24 V AC on power supply
Mounting Support	35 mm symmetrical DIN rail
Net Weight	0.55 lb(US) (0.25 kg)
Environment	
Standards	ISO 13950

Standards	ISO 13850 IEC 60947-5-1 EN/IEC 61496-1 (type 4) IEC 60204-1 EN 1088/ISO 14119
Product Certifications	TÜV UL CSA
Ip Degree Of Protection	IP20 terminals)IEC 60529 IP40 enclosure)IEC 60529
Ambient Air Temperature For Operation	14131 °F (-1055 °C)
Ambient Air Temperature For Storage	-13185 °F (-2585 °C)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	4.13 in (10.5 cm)
Package 1 Length	4.76 in (12.1 cm)
Package 1 Weight	8.89 oz (252.0 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	16
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)

Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	9.69 lb(US) (4.395 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
	Rohs Exemption Information	Yes
②	Pvc Free	

Certifications & Standards

Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration

Product data sheet

XPSAFL5130

Dimensions Drawings

Dimensions

