

# Product data sheet

Specifications



Electronic alarm, Harmony XVS, black, PNP, mounting support DIN 72, 0...90dB, 16tones, 4 channels, 12...24V DC

XVS72BMBP

## Main

|                           |                  |
|---------------------------|------------------|
| Range Of Product          | Harmony XVS      |
| Product Or Component Type | Electronic alarm |
| Device Short Name         | XVS              |

## Complementary

|  |   |
|--|---|
| Colour                                 | Black   |
| Material                               | ABS (acrylonitrile butadiene-styrene): body<br>PC (polycarbonate): terminal cover |
| Marking                                | CE  |
| Overvoltage Category                   | Class II IEC 61140  |
| Mounting Support                       | 72 mm DIN rail  |
| [Us] Rated Supply Voltage              | 12...24 V DC  |
| [Uimp] Rated Impulse Withstand Voltage | 0.8 kV  |
| Current Consumption                    | 117 mA 12 V<br>125 mA 24 V<br>158 mA 12 V<br>200 mA 24 V                          |
| Clamping Connection Capacity           | <= 1 x 1.5 mm²  |
| Width                                  | 2.83 in (72 mm)   |
| Height                                 | 2.83 in (72 mm)   |
| Depth                                  | 2.73 in (69.3 mm)   |
| Net Weight                             | 0.40 lb(US) (0.18 kg)   |

## Environment

|                                       |  |
|---------------------------------------|--|
| Discrete Output Type                  | PNP                                      |
| Signalling Type                       | 16 tones alarm                           |
| Standards                             | UL 464<br>IEC 61000-6-3<br>IEC 61000-6-2 |
| Product Certifications                | UR                                       |
| Protective Treatment                  | TC                                       |
| Ambient Air Temperature For Storage   | -31...158 °F (-35...70 °C)               |
| Ambient Air Temperature For Operation | 14...122 °F (-10...50 °C)                |
| Ip Degree Of Protection               | Panel mounted IP54 IEC 60529             |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|             |   |
|-------------|---|
| Noise Level | 0...90 dB continuous or intermittent tone)1 m |
|-------------|---|

## Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type Of Package 1       | PCE                    |
| Number Of Units In Package 1 | 1                      |
| Package 1 Height             | 5.91 in (15.0 cm)      |
| Package 1 Width              | 3.74 in (9.5 cm)       |
| Package 1 Length             | 3.74 in (9.5 cm)       |
| Package 1 Weight             | 9.38 oz (266.0 g)      |
| Unit Type Of Package 2       | S03                    |
| Number Of Units In Package 2 | 12                     |
| Package 2 Height             | 11.81 in (30.0 cm)     |
| Package 2 Width              | 11.81 in (30.0 cm)     |
| Package 2 Length             | 15.75 in (40.0 cm)     |
| Package 2 Weight             | 8.61 lb(US) (3.905 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

## Certifications & Standards

|                          |  |
|--------------------------|--|
| Reach Regulation         | <a href="#">REACH Declaration</a>                          |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a>                     |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>              |
| Circularity Profile      | <a href="#">End of Life Information</a>                    |

Dimensions Drawings

Electronic Alarm

Dimensions

