# **Product data sheet**

Specifications





# module XPSAK - Emergency stop - 24 V AC DC

XPSAK311144

- ! Discontinued on: Jun 30, 2021
- ! End-of-service on: Dec 31, 2023

① Discontinued

#### Main

Range Of Product	Preventa Safety automation
Product Or Component Type	Preventa safety module
Safety Module Name	XPSAK
Safety Module Application	For emergency stop, switch, sensing mat/edges or safety light curtain monitoring
Function Of Module	Proximity sensor monitoring
	Emergency stop monitoring 1-channel wiring
	Monitoring of electro-sensitive protection equipment (ESPE)
	Multiple emergency stop monitoring 2-channel wiring
	Monitoring of a movable guard
	Sensing mat and edges monitoring
	Emergency stop with 2 NC contacts monitoring 2-channel wiring
	Monitoring of a movable guard associated with 2 switches and automatic start
Safety Level	Can reach PL e/category 4 EN/ISO 13849-1
	Can reach SILCL 3 EN/IEC 62061
Safety Reliability Data	DC > 99 % EN/ISO 13849-1
	MTTFd = 154.5 years EN/ISO 13849-1
	PFHd = 7.39E-9 1/h EN/IEC 62061
Type Of Start	Configurable
Connections - Terminals	Captive screw clamp terminals, 1 x 0.141 x 2.5 mm² flexible with cable end, with
	double bezel
	Captive screw clamp terminals, 1 x 0.141 x 2.5 mm² solid with cable end, with
	double bezel
	Captive screw clamp terminals, 1 x 0.251 x 1.5 mm² flexible with cable end, with
	double bezel
	Captive screw clamp terminals, 1 x 0.251 x 2.5 mm² flexible with cable end, with
	double bezel
	Captive screw clamp terminals, 2 x 0.142 x 0.75 mm <sup>2</sup> flexible with cable end, with double bezel
	Captive screw clamp terminals, 2 x 0.142 x 0.75 mm² solid with cable end, with
	double bezel
	Captive screw clamp terminals, 2 x 0.252 x 1 mm² flexible with cable end, with
	double bezel
	Captive screw clamp terminals, $2 \times 0.52 \times 1.5$ mm <sup>2</sup> flexible with cable end, with double bezel
Output Type	Relay instantaneous opening, 3 NO, volt-free
Number Of Additional Circuits	1 NC + 4 solid state outputs
[Us] Rated Supply Voltage	24 V AC - 1510 %
	24 V DC - 1510 %

# Complementary

Synchronisation Time Between Inputs	Unlimited (manual start) 2 or 4 s depending of wiring (automatic start)
Supply Frequency	50/60 Hz

Apr 19, 2024 Life Is On Schneider

Maximum Power Consumption In Va	5 VA AC
Input Protection Type	Internal, electronic
[Uc] Control Circuit Voltage	24 V DC
Maximum Line Resistance	28 Ohm
Breaking Capacity	180 VA holding AC-15 C300 relay output 1800 VA inrush AC-15 C300 relay output
Breaking Capacity	1.5 A 24 V DC-13)50 ms relay output
Output Thermal Current	6 A per relay relay output
[Ith] Conventional Free Air Thermal Current	18 A
Associated Fuse Rating	4 A gG or gL relay output EN/IEC 60947-5-1, DIN VDE 0660 part 200 6 A fast blow relay output EN/IEC 60947-5-1, DIN VDE 0660 part 200
Minimum Output Current	10 mA relay output
Minimum Output Voltage	17 V relay output
Maximum Response Time On Input Open	40 ms
[Ui] Rated Insulation Voltage	300 V 2)IEC 60947-5-1 300 V 2)DIN VDE 0110 part 1
[Uimp] Rated Impulse Withstand Voltage	4 kV III IEC 60947-5-1 4 kV III DIN VDE 0110 part 1
Local Signalling	4 LEDs
Current Consumption	30 mA 24 V AC on power supply
Mounting Support	35 mm symmetrical DIN rail
Net Weight	0.66 lb(US) (0.3 kg)

## **Environment**

Standards	EN/ISO 13850 EN 1088/ISO 14119 EN/IEC 60947-5-1
	EN/IEC 60204-1
Product Certifications	CSA UL TÜV
Ip Degree Of Protection	IP20 terminals)EN/IEC 60529 IP40 enclosure)EN/IEC 60529
Ambient Air Temperature For Operation	14131 °F (-1055 °C)
Ambient Air Temperature For Storage	-13185 °F (-2585 °C)

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.56 in (6.5 cm)
Package 1 Width	4.92 in (12.5 cm)
Package 1 Length	4.13 in (10.5 cm)
Package 1 Weight	12.52 oz (355.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	12

Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	10.55 lb(US) (4.786 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

## **Product data sheet**

### XPSAK311144

#### **Dimensions Drawings**

#### **Dimensions**

