



Main

Range	Prisma
Range compatibility	Prisma P Prisma G Prisma Pack 250
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	<p>Compact : fixed INS250 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed INV250 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed NSX100...160 with earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed NSX250 with earth leakage protection - control: toggle - vertical installation</p> <p>Compact : plug-in NSX100...160 with earth leakage protection - control: toggle - vertical installation</p> <p>Compact : plug-in NSX250 with earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed NSX100...160 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed NSX250 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : plug-in NSX100...160 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : plug-in NSX250 without earth leakage protection - control: toggle - vertical installation</p> <p>Easypact : fixed CVS100...160 without earth leakage protection - control: toggle - vertical installation</p> <p>Easypact : fixed CVS250 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed INV100 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed INV160 - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed INV200 - control: direct front rotary handle - vertical installation</p> <p>Easypact : fixed CVS100...160 with earth leakage protection - control: toggle - vertical installation</p> <p>Easypact : fixed CVS250 with earth leakage protection - control: toggle - vertical installation</p>
Poles description	<p>1 x 3P : fixed : INS250 vertical installation</p> <p>1 x 3P : fixed : INV250 vertical installation</p> <p>1 x 4P : fixed : INS250 vertical installation</p> <p>1 x 4P : fixed : INV250 vertical installation</p> <p>1 x 3P : fixed : INV100 vertical installation</p> <p>1 x 3P : fixed : INV160 vertical installation</p> <p>1 x 3P : fixed : INV200 vertical installation</p> <p>1 x 4P : fixed : INV100 vertical installation</p> <p>1 x 4P : fixed : INV160 vertical installation</p> <p>1 x 4P : fixed : INV200 vertical installation</p> <p>1 x 3P : fixed : NSX100...160 vertical installation</p> <p>1 x 3P : fixed : NSX250 vertical installation</p> <p>1 x 3P : fixed : CVS100...160 vertical installation</p>

Suurim lubatud võrreldavate toodete arv on täis. Avage jaotis Võrreldavate toodete arv on täis. #LINK# ja kustutage jätkamiseks mõni toode

1 x 3P : fixed : CVS250 vertical installation
 1 x 4P : fixed : NSX100...160 vertical installation
 1 x 4P : fixed : NSX250 vertical installation
 1 x 4P : fixed : CVS100...160 vertical installation
 1 x 4P : fixed : CVS250 vertical installation
 1 x 3P : plug-in : NSX100...160 vertical installation
 1 x 3P : plug-in : NSX250 vertical installation
 1 x 4P : plug-in : NSX250 vertical installation
 1 x 4P : plug-in : NSX100...160 vertical installation

Complementary

Installation description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle - width 400 mm, depth 400 mm Pack enclosure - width 300 mm
Number of vertical modules [50 mm]	<p> 9 module(s) : CVS100...160 without earth leakage protection , direct with long terminal shield in 300 mm Wide floor-standing duct (cable coming from top or bottom of enclosure) 9 module(s) : CVS100...160 without earth leakage protection , direct with long terminal shield in 300 mm Wide wall-mounted duct (cable coming from top or bottom of enclosure) 9 module(s) : CVS100...160 without earth leakage protection , direct with long terminal shield in 300 mm Wide Pack enclosure (cable coming from top or bottom of enclosure) 9 module(s) : CVS250 without earth leakage protection , direct with long terminal shield in 300 mm Wide floor-standing duct (cable coming from top or bottom of enclosure) 9 module(s) : CVS250 without earth leakage protection , direct with long terminal shield in 300 mm Wide wall-mounted duct (cable coming from top or bottom of enclosure) 9 module(s) : CVS250 without earth leakage protection , direct with long terminal shield in 300 mm Wide Pack enclosure (cable coming from top or bottom of enclosure) 9 module(s) : INS250, direct with long terminal shield in 300 mm Wide floor-standing duct (cable coming from top or bottom of enclosure) 9 module(s) : INS250, direct with long terminal shield in 300 mm Wide wall-mounted duct (cable coming from top or bottom of enclosure) 9 module(s) : INV100, direct with long terminal shield in 300 mm Wide floor-standing duct (cable coming from top or bottom of enclosure) 9 module(s) : INV100, direct with long terminal shield in 300 mm Wide wall-mounted duct (cable coming from top or bottom of enclosure) 9 module(s) : INV160, direct with long terminal shield in 300 mm Wide floor-standing duct (cable coming from top or bottom of enclosure) 9 module(s) : INV160, direct with long terminal shield in 300 mm Wide wall-mounted duct (cable coming from top or bottom of enclosure) 9 module(s) : INV200, direct with long terminal shield in 300 mm Wide floor-standing duct (cable coming from top or bottom of enclosure) 9 module(s) : INV200, direct with long terminal shield in 300 mm Wide wall-mounted duct (cable coming from top or bottom of enclosure) 9 module(s) : INV250, direct with long terminal shield in 300 mm Wide floor-standing duct (cable coming from top or bottom of enclosure) 9 module(s) : INV250, direct with long terminal shield in 300 mm Wide wall-mounted duct (cable coming from top or bottom of enclosure) 9 module(s) : NSX100...160 without earth leakage protection , direct with long terminal shield in 300 mm Wide floor-standing duct (cable coming from top or bottom of enclosure) 9 module(s) : NSX100...160 without earth leakage protection , direct with long terminal shield in 300 mm Wide wall-mounted duct (cable coming from top or bottom of enclosure) 9 module(s) : NSX100...160 without earth leakage protection , front connection in 400 mm Wide cubicle 9 module(s) : NSX100...160 without earth leakage protection , direct with long terminal shield in 300 mm Wide Pack enclosure (cable coming from top or bottom of enclosure) 9 module(s) : NSX250 without earth leakage protection , direct with long terminal shield in 300 mm Wide floor-standing duct (cable coming from top or bottom of enclosure) 9 module(s) : NSX250 without earth leakage protection , direct with long terminal shield in 300 mm Wide wall-mounted duct (cable coming from top or bottom of enclosure) 9 module(s) : NSX250 without earth leakage protection , front connection in 400 mm Wide cubicle 9 module(s) : NSX250 without earth leakage protection , direct with long terminal shield in 300 mm Wide Pack enclosure (cable coming from top or bottom of enclosure) 13 module(s) : CVS100...160 with earth leakage protection , direct with long terminal shield in 300 mm Wide floor-standing duct (cable coming from top or bottom of enclosure) 13 module(s) : CVS100...160 with earth leakage protection , direct with long terminal shield in 300 mm Wide wall-mounted duct (cable coming from top or bottom of enclosure) 13 module(s) : CVS250 with earth leakage protection , direct with long terminal shield in 300 mm Wide floor-standing duct (cable coming from top or bottom of enclosure) 13 module(s) : CVS250 with earth leakage protection , direct with long terminal shield in 300 mm Wide wall-mounted duct (cable coming from top or bottom of enclosure) 13 module(s) : NSX100...160 with earth leakage protection , direct with long terminal shield in 300 mm Wide floor-standing duct (cable coming from top or bottom of enclosure) 13 module(s) : NSX100...160 with earth leakage protection , direct with long terminal shield in 300 mm Wide wall-mounted duct (cable coming from top or bottom of enclosure) </p>

11 module(s) : NSX100...160 with earth leakage protection , front connection in 400 mm Wide cubicle
 13 module(s) : NSX100...160 with earth leakage protection , direct with long terminal shield in 300 mm Wide Pack enclosure (cable coming from top or bottom of enclosure)
 13 module(s) : NSX250 with earth leakage protection , direct with long terminal shield in 300 mm Wide floor-standing duct (cable coming from top or bottom of enclosure)
 13 module(s) : NSX250 with earth leakage protection , direct with long terminal shield in 300 mm Wide wall-mounted duct (cable coming from top or bottom of enclosure)
 11 module(s) : NSX250 with earth leakage protection , front connection in 400 mm Wide cubicle
 13 module(s) : NSX250 with earth leakage protection , direct with long terminal shield in 300 mm Wide Pack enclosure (cable coming from top or bottom of enclosure)

Condition of using cable tie	Need additional plate (1M high) when installation of device is in vertical
Height	250 mm
Product weight	0.54 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

Standards	IEC 61439-2
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Toote keskkonnaprofil
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------