

Product data sheet

Specifications



Multisound siren, Harmony XVS, white colour, 106dB, 2tones, 230V AC

XVS10MMW

Main

Range Of Product	Harmony XVS
Product Or Component Type	Siren
Device Short Name	XVS
Colour	White
Signalling Type	2 tones siren
[Us] Rated Supply Voltage	230 V AC
Noise Level	106 dB continuous or intermittent tone)1 m

Complementary

Material	PC: body
Net Weight	2.20 lb(US) (1 kg)
Marking	CE
[Uimp] Rated Impulse Withstand Voltage	4 kV
Current Consumption	40 mA 230 V
Clamping Connection Capacity	<= 1 x 1.5 mm²
Electrical Connection	Cable 0.26...0.33 in (6.5...8.5 mm)
Width	4.49 in (114 mm)
Height	4.49 in (114 mm)
Depth	6.03 in (153.2 mm)

Environment

Standards	IEC 60947-1 IEC 60947-5-1
Protective Treatment	TC
Ambient Air Temperature For Storage	-31...158 °F (-35...70 °C)
Ambient Air Temperature For Operation	-22...122 °F (-30...50 °C)
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP53

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	7.68 in (19.500 cm)
Package 1 Width	5.51 in (14.000 cm)
Package 1 Length	5.51 in (14.000 cm)
Package 1 Weight	2.74 lb(US) (1.242 kg)
Unit Type Of Package 2	S04
Number Of Units In Package 2	8
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	15.75 in (40.000 cm)
Package 2 Length	23.62 in (60.000 cm)
Package 2 Weight	24.49 lb(US) (11.109 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	32
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	118.96 lb(US) (53.960 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End of Life Information	

Dimensions Drawings

Siren

Dimensions

