

Fiche Produit

Spécifications

SQUARE 



Non-Reversing Starter Size 3, 3-Pole, Melting Alloy Overload, NEMA 1 +Options

8536SEG1V84CFF4G11T

Principal

Type De Produit	Starter
Gamme De Produit	S
Starter Type	Non réversible

Complémentaire

Nema Size	3
Courant Nominal	90 A
Nombre De Pôles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phases
Type Of Overload	Melting alloy 3
Horsepower Rating	25 HPà 200 V AC 30 HPà 230 V AC 50 HPà 460 V AC 50 HPà 575 V AC
Coil Voltage	120 V AC 60 Hz circuit secondaire 208 V AC 60 Hz circuit primaire
Control Circuit Type	Control circuit transformer
Control Units	Selector switch (HAND-OFF-AUTO)
Autre Équipement	2 fuses (primary), 1 fuse (secondary)
Terminal Type	Borniers à vis-étrier

Environnement

Enclosure Type	NEMA 1 feuille d'acier peint
Certifications	listé UL NEMA CSA

Garantie contractuelle

Garantie	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications