Product datasheet

Specification





switch disconnector, Compact INS1000, 1000 A, standard version with black rotary handle, 3 poles

31332

Main

IVIAIII	
Range	ComPact
Product Name	ComPacT INS
Product Or Component Type	Switch disconnector
Poles Description	3P
Network Type	AC DC
Network Frequency	50/60 Hz
[le] Rated Operational Current	AC-21A: 1000 A AC 50/60 Hz 220/240 V AC-21A: 1000 A AC 50/60 Hz 380/415 V AC-21A: 1000 A AC 50/60 Hz 440/480 V AC-21A: 1000 A AC 50/60 Hz 480 V NEMA AC-21A: 1000 A AC 50/60 Hz 500/525 V AC-21A: 1000 A AC 50/60 Hz 660/690 V AC-22A: 1000 A AC 50/60 Hz 220/240 V AC-22A: 1000 A AC 50/60 Hz 380/415 V AC-22A: 1000 A AC 50/60 Hz 440/480 V AC-22A: 1000 A AC 50/60 Hz 440/480 V AC-22A: 1000 A AC 50/60 Hz 480 V NEMA AC-22A: 1000 A AC 50/60 Hz 660/690 V AC-22A: 1000 A AC 50/60 Hz 500/525 V AC-22A: 1000 A AC 50/60 Hz 660/690 V AC-23A: 1000 A AC 50/60 Hz 660/690 V AC-23A: 1000 A AC 50/60 Hz 380/415 V AC-23A: 1000 A AC 50/60 Hz 440/480 V AC-23A: 1000 A AC 50/60 Hz 40/480 V AC-23A: 1000 A AC 50/60 Hz 500/525 V AC-22A: 1000 A AC 50/60 Hz 660/690 V AC-23A: 1000 A AC 50/60 Hz 60/60 Hz 60/600 V AC-23A: 1000 A AC 50/60 Hz 660/690 V AC-23A: 1000 A AC 50/60 Hz 500/525 V AC-22A: 1000 A AC 50/60 Hz 500/525 V AC-22A: 1000 A AC 50/60 Hz 660/690 V AC-23A: 1000 A AC 50/60 Hz 500/525 V AC-22A: 1000 A AC 50/60 Hz 500/525 V AC-22A: 1000 A AC 50/60 Hz 660/690 V AC-23A: 1000 A AC 50/60 Hz 660/690 V AC-23A: 1000 A AC 50/60 Hz 660/690 V AC-23A: 1000 A DC 125 V 2 poles in series AC-22A: 1000 A DC 125 V 2 poles in series AC-23A: 1000 A DC 125 V 2 poles in series
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	12 kV
[Ith] Conventional Free Air Thermal Current	1000 A at 60 °C
[Icm] Rated Short-Circuit Making Capacity	330 kA with upstream protection circuit breaker 690 V AC at 50/60 Hz 75 kA switch-disconnector alone 690 V AC at 50/60 Hz
[Ue] Rated Operational Voltage	125 V DC 690 V AC 50/60 Hz
Suitability For Isolation	Yes
Contact Position Indicator	Yes
Visible Break	No
Pollution Degree	3

Complementary

Control Type Direct front rotary handle

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Handle Colour	Black
Mounting Mode	Fixed
Mounting Support	Rail Plate
Upside Connection	Front
Downside Connection	Front
Maximum Power	AC-23: 315 kW at 220/240 V AC 50/60 Hz AC-23: 560 kW at 380/400 V AC 50/60 Hz AC-23: 630 kW at 415 V AC 50/60 Hz AC-23: 710 kW at 500/525 V AC 50/60 Hz AC-23: 900 kW at 660/690 V AC 50/60 Hz
Rated Duty	Uninterrupted
Intermittent Duty Class	Class 120 - 60 %
[Icw] Rated Short-Time Withstand Current	10 kA during 20 s conforming to IEC 60947-3 20 kA during 3 s conforming to IEC 60947-3 35 kA during 1 s conforming to IEC 60947-3 42 kA during 0.8 s conforming to IEC 60947-3 50 kA during 0.5 s conforming to IEC 60947-3 8 kA during 30 s conforming to IEC 60947-3
Mechanical Durability	3000 cycles
Electrical Durability	AC-21A: 500 cycles 220/240 V AC 50/60 Hz AC-21A: 500 cycles 380/415 V AC 50/60 Hz AC-21A: 500 cycles 440/480 V AC 50/60 Hz AC-21A: 500 cycles 480 V AC 50/60 Hz AC-21A: 500 cycles 500/525 V AC 50/60 Hz AC-21A: 500 cycles 660/690 V AC 50/60 Hz AC-21A: 500 cycles 660/690 V AC 50/60 Hz AC-22A: 500 cycles 380/415 V AC 50/60 Hz AC-22A: 500 cycles 380/415 V AC 50/60 Hz AC-22A: 500 cycles 380/415 V AC 50/60 Hz AC-22A: 500 cycles 440/480 V AC 50/60 Hz AC-22A: 500 cycles 480 V AC 50/60 Hz AC-22A: 500 cycles 500/525 V AC 50/60 Hz AC-22A: 500 cycles 660/690 V AC 50/60 Hz AC-22A: 500 cycles 660/690 V AC 50/60 Hz AC-23A: 500 cycles 220/240 V AC 50/60 Hz AC-23A: 500 cycles 380/415 V AC 50/60 Hz AC-23A: 500 cycles 380/415 V AC 50/60 Hz AC-23A: 500 cycles 440/480 V AC 50/60 Hz AC-23A: 500 cycles 480 V AC 50/60 Hz AC-23A: 500 cycles 500/525 V AC 50/60 Hz AC-23A: 500 cycles 500/525 V AC 50/60 Hz AC-23A: 500 cycles 125 V DC 2 poles in series DC-22A: 500 cycles 125 V DC 2 poles in series
Connection Pitch	70 mm
Height	300 mm
Width	340 mm
Depth	146.5 mm
Net Weight Environment	14 kg
Standards	IEC 60947-1 IEC 60947-3
Product Certifications	KEMA-KEUR
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to EN 50102
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.000 cm
Package 1 Width	40.000 cm
Package 1 Length	60.000 cm
Package 1 Weight	16.134 kg

Contractual warranty

Apr 25, 2024

Warranty 18 months

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Apr 25, 2024