## **Product datasheet**

Specification





# C60 - circuit breaker - C60L - 4P - 50A - C curve

25455

! Discontinued on: Jan 23, 2021

(!) Discontinued

#### Main

Range Of Product	C60
Range	Multi9
Product Name	C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60L
Device Application	Distribution
Poles Description	4P
Number Of Protected Poles	4
[In] Rated Current	50 A at 40 °C
Network Type	DC AC
Trip Unit Technology	Thermal-magnetic
Curve Code	С
Breaking Capacity	20 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 50 kA Icu at 230240 V AC 50/60 Hz conforming to EN/IEC 60947-2 25 kA Icu at 400415 V AC 50/60 Hz conforming to EN/IEC 60947-2 30 kA Icu at 125 V DC 2P conforming to EN/IEC 60947-2 50 kA Icu at 125 V DC 3P conforming to EN/IEC 60947-2 60 kA Icu at <= 250 V DC 4P conforming to EN/IEC 60947-2
Suitability For Isolation	Yes conforming to IEC 60947-2

#### Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	440 V AC 50/60 Hz 230240 V AC 50/60 Hz 400415 V AC 50/60 Hz <= 250 V DC
Magnetic Tripping Limit	710 x ln
[Ics] Rated Service Breaking Capacity	10 kA conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 25 kA conforming to EN/IEC 60947-2 - 230240 V AC 50/60 Hz 12.5 kA conforming to EN/IEC 60947-2 - 400415 V AC 50/60 Hz
Limitation Class	3 conforming to EN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mounting Support	35 mm symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	NO
9 Mm Pitches	8
Height	81 mm
Width	72 mm
Depth	73 mm
Net Weight	0.48 kg
Mechanical Durability	20000 cycles
Connections - Terminals	Tunnel type terminals25 mm² flexible Tunnel type terminals35 mm² rigid
Tightening Torque	Power circuit: 3.5 N.m upside 3.5 N.m downside
Earth-Leakage Protection	Separate block
Product Compatibility	C60 accessories C60 auxiliary

## **Environment**

Standards	EN 60898 EN/IEC 60947-2
Ip Degree Of Protection	IP20 conforming to IEC 60529
Overvoltage Category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-2560 °C
Ambient Air Temperature For Storage	-4070 °C

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	7.2 cm
Package 1 Length	7.3 cm
Package 1 Weight	0.477 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins